

PNOZ s20 C 24VDC 2so

751160



PNOZsigma Contact expansion. Outputs: 2 semiconductor safety outputs, 1 standard semiconductor output, UB 24 V DC, width: 22.5 mm, plug-in spring-loaded terminals. Expansion module for expansion in connection with safety- related control components.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Application options:	Instantaneous contact expansion
Supply voltage (V):	24,0
Terminal type:	Spring-loaded terminal
Terminal style:	Plug-in
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Number of instantaneous safety contacts:	0
Number of instantaneous safety outputs:	2 ST
Width dimension:	22.5 mm
Height dimension:	100.0 mm
Depth dimension:	120.0 mm
Gross weight:	130 g
Net weight:	120 g
Ambient temperature:	-10 - 55 °C

Optional accessories



750020

PNOZ s connector (10 pieces)



751004

PNOZ s Setspring loaded terminals 22,5mm



750010

PNOZ s terminator plug (10 pieces)