

PNOZ s7.2 C 24VDC 4 n/o 1 n/c expand

751177



PNOZsigma Contact expansion. Outputs: 4 N/O, 1 N/C UB 24 V DC, width: 17.5 mm, plug-in spring-loaded terminals. Contact block for contact expansion in connection with safety-related control components. Additional mounting of modules on the right is possible.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;CCC
Application options:	Instantaneous contact expansion
Max. current at DC1:	6.0 A
Voltage at AC1:	240 V
Terminal type:	Spring-loaded terminal
Terminal style:	Plug-in
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Operating modes:	Single-channel;without detection of shorts across contacts
Number of instantaneous safety contacts:	4
Number of instantaneous safety outputs:	0 ST
Width dimension:	17.5 mm
Height dimension:	100.0 mm
Depth dimension:	120.0 mm
Gross weight:	185 g
Net weight:	170 g
Ambient temperature:	-10 - 55 °C

Optional accessories



750020

PNOZ s connector (10 pieces)



751003

PNOZ s Setspring loaded terminals 17,5mm



750010

PNOZ s terminator plug (10 pieces)