

**PNOZ s4 C 24VDC 3 n/o 1 n/c coated**

**751184**



PNOZsigma Safety relay (standalone). Inputs: 1-/2-channel wiring with/without detection of shorts across contacts. Outputs: 3 N/O, 1 N/C, 1 semiconductor UB 24 V DC, width: 22.5 mm, plug-in spring-loaded terminals. Monitoring E-STOP, safety gates.

**Technical details**

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;KOSHA;CCC
Application options:	Instantaneous E-STOP monitoring;Limit switch;Light beam device mon. Type 2 with t/p;Light beam device mon. Type 2 w/o t/p;Light beam device mon. Type 4;Safety gate monitor
Operating modes:	Single-channel;Automatic reset;Dual-channel;Manual reset;Detection of shorts across contacts;Start-up testing;Monitored manual reset;without detection of shorts across contacts;Self test
Product standard:	EN 60947-5-1
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Supply voltage (V):	24,0
Supply voltage type:	DC
Terminal style:	Plug-in
Terminal type:	Spring-loaded terminal
Number of instantaneous safety contacts:	3
Number of delayed safety contacts:	0
Number of auxiliary contacts:	1
Number of semiconductor outputs:	1
Stop category:	0
Max. current at DC13 I (6 cycles/min):	5.0 A
Max. current at AC15:	5.0 A
Width dimension:	22.5 mm
Height dimension:	100.0 mm

Depth dimension:	120.0 mm
Gross weight:	200 g
Net weight:	190 g
Ambient temperature:	-25 - 55 °C

## Optional accessories



751004

PNOZ s Setspring loaded terminals 22,5mm



750900

PNOZ s pIE



750910

PNOZ s nIE



750010

PNOZ s terminator plug ( 10 pieces)