

## PNOZ m ES Powerlink

772119



Configurable control system PNOZmulti 2 expansion module  
Communication module POWERLINK.

### Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian)
Fieldbus interface:	Ethernet POWERLINK V2
Fieldbus connection:	RJ45
Transmission rate:	100 MBit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	100 g
Net weight:	90 g
Ambient temperature:	0 - 60 °C

### Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.

## Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.

## Alternatives



772135

PNOZ m ES CC-Link



772138

PNOZ m ES Profinet



772136

PNOZ m ES EtherCAT



772137

PNOZ m ES EtherNet/IP



772134

PNOZ m ES CANopen



772132

PNOZ m ES Profibus

---