



Safe communication module SafetyNET p for PNOZ m Bxp

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV
Fieldbus interface:	SafetyNET p
Version for extreme environ. conditions:	Standard
Width dimension:	45.0 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	190 g
Net weight:	180 g
Ambient temperature:	0 - 60 °C

Accessories



380000

SafetyNET p Cable per mtr



380401

RJ45 Connector



750017

Set 5 Screw Terminals



751017

Set 5 Spring Terminals

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)

Alternatives



772120

PNOZ m EF Multi Link

Related Products



773616

PDP67 F 8DI ION PT



773615

PDP67 F 8DI ION HP VA



773614

PDP67 F 8DI ION VA



773601

PDP67 F 8DI ION HP



773600

PDP67 F 8DI ION



772171

PNOZ m EF 2MM



772170

PNOZ m EF 1MM



772160

PNOZ m EF 4AI



772144

PNOZ m EF 8DI2DOT



772143

PNOZ m EF 4DI4DOR



772142

PNOZ m EF 8DI4DO



772140

PNOZ m EF 16DI



772138

PNOZ m ES Profinet



772137

PNOZ m ES EtherNet/IP



772136

PNOZ m ES EtherCAT



772135

PNOZ m ES CC-Link



772134

PNOZ m ES CANopen



772132

PNOZ m ES Profibus



772131

PNOZ m ES RS232



772130

PNOZ m ES ETH



772121

PNOZ m EF PDP Link



772120

PNOZ m EF Multi Link



772119

PNOZ m ES Powerlink



772101

PNOZ m B1



772100

PNOZ m B0