

PNOZ m ES CC-Link

772135



Configurable control system PNOZmulti 2 expansion module
Communication interface CC-Link.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian)
Fieldbus interface:	CC-Link V1.10
Fieldbus connection:	5-pin Combicon plug-in connector
Fieldbus type:	Slave
Transmission rate:	10 MBit/s;156 kbit/s;2,5 MBit/s;5 MBit/s;625 kbit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	110 g
Net weight:	90 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.

Alternatives



772138

PNOZ m ES Profinet



772136

PNOZ m ES EtherCAT



772137

PNOZ m ES EtherNet/IP



772134

PNOZ m ES CANopen



772132

PNOZ m ES Profibus



772119

PNOZ m ES Powerlink

Related Products



773616

PDP67 F 8DI ION PT



773615

PDP67 F 8DI ION HP VA



773614

PDP67 F 8DI ION VA



773601

PDP67 F 8DI ION HP



773600

PDP67 F 8DI ION



772171

PNOZ m EF 2MM



772170

PNOZ m EF 1MM



772160

PNOZ m EF 4AI



772144

PNOZ m EF 8DI2DOT



772143

PNOZ m EF 4DI4DOR



772142

PNOZ m EF 8DI4DO



772140

PNOZ m EF 16DI



772131

PNOZ m ES RS232



772130

PNOZ m ES ETH



772122

PNOZ m EF SafetyNET



772121

PNOZ m EF PDP Link



772120

PNOZ m EF Multi Link



772101

PNOZ m B1



772100

PNOZ m B0
