

PNOZ m ES EtherNet/IP

772137



Configurable control system PNOZmulti 2 expansion module
Communication interface EtherNet/IP.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian)
Fieldbus interface:	EtherNet/IP (TM)
Fieldbus type:	Adapter
Transmission rate:	10 MBit/s;100 MBit/s
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	110.4 mm
Gross weight:	100 g
Net weight:	90 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793543

Screw terminals PNOZ mmcxp, 10 pcs.



783543

Spring terminals PNOZ mmcxp, 10 pcs.

Alternatives



772135

PNOZ m ES CC-Link



772138

PNOZ m ES Profinet



772136

PNOZ m ES EtherCAT



772134

PNOZ m ES CANopen



772132

PNOZ m ES Profibus



772119

PNOZ m ES Powerlink
