

PNOZ m EF 4AI

772160



Configurable control system PNOZmulti 2 expansion module 4 safe analogue inputs 4..20 mA, single use possible, two inputs usable up to SIL3/PLe.

Technical details

Certifications:	CE;cULus Listed;EAC (Eurasian);TÜV;KOSHA
Number of analogue inputs:	4
Type of analogue inputs:	Strom
Supply voltage 2 (V):	24
Supply voltage type 2:	DC
Terminal type:	Screw terminal;Spring-loaded terminal
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	117 g
Net weight:	108 g
Ambient temperature:	0 - 60 °C

Accessories



750004

PNOZ s Setscrew terminals 22,5mm



751004

PNOZ s Setspring loaded terminals 22,5mm

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)

Related Products



773616

PDP67 F 8DI ION PT



773615

PDP67 F 8DI ION HP VA



773614

PDP67 F 8DI ION VA



773601

PDP67 F 8DI ION HP



773600

PDP67 F 8DI ION



772171

PNOZ m EF 2MM



772170

PNOZ m EF 1MM



772144

PNOZ m EF 8DI2DOT



772143

PNOZ m EF 4DI4DOR



772142

PNOZ m EF 8DI4DO



772140

PNOZ m EF 16DI



772138

PNOZ m ES Profinet



772137

PNOZ m ES EtherNet/IP



772136

PNOZ m ES EtherCAT



772135

PNOZ m ES CC-Link



772134

PNOZ m ES CANopen



772132

PNOZ m ES Profibus



772131

PNOZ m ES RS232



772130

PNOZ m ES ETH



772122

PNOZ m EF SafetyNET



772121

PNOZ m EF PDP Link



772120

PNOZ m EF Multi Link



772119

PNOZ m ES Powerlink



772101

PNOZ m B1



772100

PNOZ m B0
