

PNOZ m ES 14DO

772181



module with 14 non safe semiconductor outputs

Technical details

Certifications:	CE
Positive switching 1-pole SC output:	14
Supply voltage 2 (V):	24
Supply voltage type 2:	DC
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	110 g
Net weight:	100 g
Ambient temperature:	0 - 60 °C

Accessories



750004

PNOZ s Setscrew terminals 22,5mm



751004

PNOZ s Setspring loaded terminals 22,5mm

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)
