

PDP67 F 8DI ION

773600



Decentralised input module IP67 for PNOZmulti.

Technical details

Certifications:	CE;cULus Listed;BG;TÜV
Application range:	Standard/failsafe
Protection type, housing:	IP67
Terminal protection type:	IP67
Width dimension:	60.0 mm
Height dimension:	133.0 mm
Depth dimension:	30.0 mm
Gross weight:	270 g
Net weight:	250 g
Ambient temperature:	-30 - 60 °C

Accessories



630297

PSEN op cable axial M12 5-pole 30m



630310

PSEN op cable axial M12 5-pole 3m



630311

PSEN op cable axial M12 5-pole 5m



630312

PSEN op cable axial M12 5-pole 10m



630298

PSEN cable M12-5sf 20m

Optional accessories



380200

PSS67 Cable M8sf M12sm, 3m



380201

PSS67 Cable M8sf M12sm, 5m

380202

PSS67 Cable M8sf M12sm, 10m



380203

PSS67 Cable M8sf M12sm, 30m



380208

PSS67 Cable M12sf M12sm, 3m



380209

PSS67 Cable M12sf M12sm, 5m



380210

PSS67 Cable M12sf M12sm, 10m



380211

PSS67 Cable M12sf M12sm, 30m



380250

PSS67 Supply Cable IN sf OUT sm, B, 3m



380251

PSS67 Supply Cable IN sf OUT sm, B, 5m



380252

PSS67 Supply Cable IN sf OUT sm, B, 10m



380256

PSS67 Supply Cable IN sf, B, 3m



380257

PSS67 Supply Cable IN sf, B, 5m



380258

PSS67 Supply Cable IN sf, B, 10m



380300

PSEN ma adapter



380301

PSEN cs adapter



380708

PDP67 cable M12-5sm, 30m



380220

PSS67 cable M12-5sf, M12-5sm, 20m



380707

PDP67 cable M12-5sm, 20m



380706

PDP67 cable M12-5sm, 10m



380705

PDP67 cable M12-5sm, 3m



380709

PDP67 cable M12-5sm, 5m



380325

PSEN sl adapter