

PMCProtego D.12/000/0/P/2/110-230VAC

8176815



Technical Details at 3 x 230 V AC supply voltage: Permanent output current: 12,0 A; I_{max} (2 sec.) = 30,0 A; I_{max} (5 sec.) = 24,0 A; Power consumption in S1 operation: 4,5 kVA Internal brake resistor and mains filter

Technical details

Certifications:	CE;EAC (Eurasian);TÜV
Hardware option 1:	0 = Without
Hardware option 2:	0 = Without
Hardware option 3:	0 = Without
Firmware option:	2 = EtherCat
Supply voltage (V):	110,0 - 230,0
Continuous output current at 3x230V:	12.0 A
Output stage clock frequency:	8 kHz
Peak current:	30.00 A
Peak output current max. 5s:	24.00 A
Supply voltage 2 (V):	24
Supply voltage type 2:	DC
Number of STO-Enables:	2
Number of digital inputs:	4
Number of analogue inputs:	2
Number of CANopen interfaces:	1
Width dimension:	70.0 mm
Height dimension:	345.0 mm
Depth dimension:	243.0 mm
Gross weight:	5500 g

Net weight:	4400 g
Ambient temperature:	0 - 40 °C