

PMctendo SZ.44/0/2/2/7/K/H/30/00

8177074

Mo = 8,6Nm Io = 6,60A UN = 400V nN = 3000min-1 Jmot = 2,98 kgcm2  
Encoder EQN 1135 EnDat2.2 multiturn; without brake;



## Technical details

Certifications:	CE
Motor size:	44
Standstill torque:	8.60 Nm
Rated load torque:	6.90 Nm
Peak torque:	29.00 Nm
Standstill current:	6.60 A
Nominal voltage:	5.80 A
Peak current:	35.00 A
Rated speed (RPM):	3000 rpm
Rated voltage:	400 V
Moment of inertia:	2.98 kgcm <sup>2</sup>
Brake:	No
Feedback:	2 = Endat2.2 optical multi-turn
Motor connection:	Angled swivel connector
Connection direction:	To A-end
Cooling:	0 = Convection
Type of motor shaft:	without feather key
Longueur d'arbre:	40 mm
Flange dimension:	98 mm
Overall motor length:	216 mm

Centering diameter:	95 mm
Pitch circle diameter:	115 mm
Number of poles:	14
Protection type, housing:	IP56
Gross weight:	8600 g
Net weight:	7200 g