

S1WP 9A 110-230VAC/DC UM 0-550VACDC Ts=0

890071



True power monitoring for 1- and 3-phase mains Suitable for frequency-controlled electrical machines; 9 measuring ranges 0 - 1000 Hz; Measuring voltage 0 - 550 V AC/DC, start-up suppression time 0 s. 1 changeover output, 1 analogue output 0 - 10 V DC or 4 - 20 mA.

Technical details

Certifications:	CE;cULus Listed;CCC
Application options:	True power measurement
Supply voltage (V):	230,0
Supply voltage type:	AC
Measuring voltage:	0 - 550
Measuring current:	9
Terminal type:	Screw terminal
Terminal style:	fixed
Number of auxiliary contacts:	1
Width dimension:	22.5 mm
Height dimension:	87.0 mm
Depth dimension:	121.0 mm
Gross weight:	150 g
Net weight:	140 g
Ambient temperature:	0 - 55 °C