

## Connector/CA/M12-5SMX/A/TR

C1000058



Terminating plug with a 120  $\Omega$  resistor between Pin 4 and Pin 5. Suitable for the Interface: CANopen.

## Technical details

### General data

Approval: CE, UKCA, cULus Listed

### Technical data

### Electrical data

Rated current: 4 A

### Environmental data

Ambient temperature: -30 - 80 °C

Clearance & creepage dist. to: IEC 60664-1

Pollution degree clear.&creep.: 2

### Mechanical data

Connector type 1: 5-pin M12 male connector

Shape of connector type 1: straight

Coding of M12 connector 1: A coded

Matl threaded ring conn 1: GD-Zn, Ni

Contact surfaces material 1: CuZn, Ni b/Au 0.2 gal.

Housing colour: Black

Approvals for connector 1: UL 94 HB

Net weight: 11 g

Gross weight: 12 g

### Environment

WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85366990
UNSPSC 25:	26121603
EAN-Code:	4046548105032
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27279090
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC003015
Volume:	0 dm3