

Unmonitored PIT si1.1




Muting lamp in accordance with EN 61496 and VDE 0113-201

Features

- Signal lamp for muting mode
- Protection type IP65

Approvals

	PIT si1.1
	●

Technical details **PIT si1.1**

Electrical data

Supply voltage	24 VDC
Voltage tolerance	+/-15 %
Power consumption	7 W
Bulb	Type BA 15d, 24 VDC, 7 W

Environmental data

Ambient temperature	-25 ... +50 °C
Storage temperature	-25 ... +50 °C

Mechanical data

Housing material	
Cover	PC clear
Base	ABS black
Dimensions	
Diameter	100 mm
Height	138.5 mm
Mounting position	Vertical
Cable entry	ISO 20 mm
Max. cross section of external conductors	
Single-core, flexible with crimp connectors	0.75 ... 1.5 mm ²
Connection type	Spring-loaded terminal
Protection type	IP65

Order reference

Type	Order no.
PIT si1.1 incl. bulb, angle bracket and 2 screws	620 010

Order reference for accessories

Type	Order no.
Bulb	620 100

Description

In muting mode, the operator must be made aware of the hazard that results from the suspension of the safety function. The PIT si1.1 muting lamp is designed for this purpose. It illuminates as soon as muting mode is started.