



		With external rubber gasket	With external rubber gasket	Other rollers available. See on page 56	Round rod, Ø 3 mm, stainless steel
Contact type:					
Contact blocks					
3	R	FC 321-M2	1NO-1NC	FC 331-M2	1NO-1NC
33	L	FC 3321-M2	1NO+1NC	FC 3331-M2	1NO+1NC
34	L	FC 3421-M2	2NC	FC 3431-M2	2NC
Max. speed		1 m/s	1 m/s	page 237 - type 1	1.5 m/s
Min. force		0.06 Nm	0.1 Nm	0.09 Nm (0.25 Nm \ominus)	0.09 Nm
Travel diagrams		page 238 - group 3	page 238 - group 3	page 238 - group 4	page 238 - group 4

		Square rod, 3x3 mm	Other rollers available. See on page 56	Fiber glass rod	
Contact blocks					
Contact blocks					
3	R	FC 333-M2	1NO-1NC	FC 335-M2	1NO-1NC
33	L	FC 3333-M2	1NO+1NC	FC 3335-M2	1NO+1NC
34	L	FC 3433-M2	2NC	FC 3435-M2	2NC
Max. speed		1.5 m/s	1 m/s	page 237 - type 1	1.5 m/s
Min. force		0.09 Nm	0.09 Nm	0.09 Nm (0.25 Nm \ominus)	0.09 Nm
Travel diagrams		page 238 - group 4	page 238 - group 4	page 238 - group 4	page 238 - group 4

		Other rollers available. See on page 56	Other rollers available. See on page 56	Porcelain roller	Other rollers available. See on page 56
Contact blocks					
Contact blocks					
3	R	FC 351-M2	1NO-1NC	FC 353-E11M2	1NO-1NC
33	L	FC 3351-M2	1NO+1NC	FC 3353-E11M2V9	1NO+1NC
34	L	FC 3451-M2	2NC	FC 3453-E11M2V9	2NC
Max. speed		page 237 - type 1	page 237 - type 1	0.5 m/s	page 237 - type 1
Min. force		0.05 Nm (0.25 Nm \ominus)	0.05 Nm (0.25 Nm \ominus)	0.02 Nm (0.25 Nm \ominus)	0.09 Nm (0.25 Nm \ominus)
Travel diagrams		page 238 - group 4	page 238 - group 4	page 238 - group 5	page 238 - group 4

⁽¹⁾ Positive opening only with actuator set to max. See page 55.

All measures in the drawings are in mm

Items with code on **green** background are stock items

Accessories See page 225