



Contact type:	With stainless steel roller on request	With stainless steel roller on request	With stainless steel roller on request	Square rod, 3x3 mm, stainless steel
R = snap action L = slow action				
Contact blocks				
B11 R	NA B112KG-DN2 (1NO+1NC)	NA B112KH-DN2 (1NO+1NC)	NA B112KP-DN2 (1NO+1NC)	NA B112LB-DN2 (1NO+1NC)
B02 R	NA B022KG-DN2 (2NC)	NA B022KH-DN2 (2NC)	NA B022KP-DN2 (2NC)	NA B022LB-DN2 (2NC)
B12 R	NA B122KG-DN2 (1NO+2NC)	NA B122KH-DN2 (1NO+2NC)	NA B122KP-DN2 (1NO+2NC)	NA B122LB-DN2 (1NO+2NC)
B22 R	NA B222KG-DN2 (2NO+2NC)	NA B222KH-DN2 (2NO+2NC)	NA B222KP-DN2 (2NO+2NC)	NA B222LB-DN2 (2NO+2NC)
G11 L	NA G112KG-DN2 (1NO+1NC)	NA G112KH-DN2 (1NO+1NC)	NA G112KP-DN2 (1NO+1NC)	NA G112LB-DN2 (1NO+1NC)
G02 L	NA G022KG-DN2 (2NC)	NA G022KH-DN2 (2NC)	NA G022KP-DN2 (2NC)	NA G022LB-DN2 (2NC)
G12 L	NA G122KG-DN2 (1NO+2NC)	NA G122KH-DN2 (1NO+2NC)	NA G122KP-DN2 (1NO+2NC)	NA G122LB-DN2 (1NO+2NC)
G22 L	NA G222KG-DN2 (2NO+2NC)	NA G222KH-DN2 (2NO+2NC)	NA G222KP-DN2 (2NO+2NC)	NA G222LB-DN2 (2NO+2NC)
Max. speed	page 243 - type 1	page 243 - type 1	page 243 - type 1	1.5 m/s
Min. force	0.07 Nm (0.25 Nm ⊕)	0.07 Nm (0.25 Nm ⊕)	0.07 Nm (0.25 Nm ⊕)	0.07 Nm
Travel diagrams	page 244 - group 5	page 244 - group 5	page 244 - group 5	page 244 - group 5

Contact blocks	Round rod, Ø 3 mm, stainless steel	Fiber glass rod		Porcelain roller
B11 R	NA B112LE-DN2 (1NO+1NC)	NA B112LH-DN2 (1NO+1NC)	NA B112LL-DN2 (1NO+1NC)	NA B112LP-DN2E24 (1NO+1NC)
B02 R	NA B022LE-DN2 (2NC)	NA B022LH-DN2 (2NC)	NA B022LL-DN2 (2NC)	NA B022LP-DN2E24 (2NC)
B12 R	NA B122LE-DN2 (1NO+2NC)	NA B122LH-DN2 (1NO+2NC)	NA B122LL-DN2 (1NO+2NC)	NA B122LP-DN2E24 (1NO+2NC)
B22 R	NA B222LE-DN2 (2NO+2NC)	NA B222LH-DN2 (2NO+2NC)	NA B222LL-DN2 (2NO+2NC)	NA B222LP-DN2E24 (2NO+2NC)
G11 L	NA G112LE-DN2 (1NO+1NC)	NA G112LH-DN2 (1NO+1NC)	NA G112LL-DN2 (1NO+1NC)	NA G112LP-DN2E24 (1NO+1NC)
G02 L	NA G022LE-DN2 (2NC)	NA G022LH-DN2 (2NC)	NA G022LL-DN2 (2NC)	NA G022LP-DN2E24 (2NC)
G12 L	NA G122LE-DN2 (1NO+2NC)	NA G122LH-DN2 (1NO+2NC)	NA G122LL-DN2 (1NO+2NC)	NA G122LP-DN2E24 (1NO+2NC)
G22 L	NA G222LE-DN2 (2NO+2NC)	NA G222LH-DN2 (2NO+2NC)	NA G222LL-DN2 (2NO+2NC)	NA G222LP-DN2E24 (2NO+2NC)
Max. speed	1.5 m/s	1.5 m/s	1.5 m/s	0.5 m/s
Min. force	0.07 Nm	0.07 Nm	0.07 Nm	0.04 Nm
Travel diagrams	page 244 - group 5	page 244 - group 5	page 244 - group 5	page 244 - group 5

All measures in the drawings are in mm