



PRODUCT-DETAILS**SH710AMV****A10 SIDE ENT 1-POST HOOD 1XPG21-3/4**

General Information

Extended Product Type:	SH710AMV
Product ID:	7TAA080240R0080
Catalog Description:	A10 SIDE ENT 1-POST HOOD 1XPG21-3/4
Long Description:	Side entry single post hood, NPT entry-1 Inch x 3/4 Inch
Display Name:	SH710AMV

Ordering

UPC:	786209987716
Country of Origin:	Germany
Selling Unit of Measure:	each

Container Information

Package Level 1 Units:	10 EA
-------------------------------	-------

Package Level 1 Width:	177.8 mm 7 in
Package Level 1 Height:	127 mm 5 in
Package Level 1 Depth / Length:	311.15 mm 12.25 in

Additional Information

Brand / Label:	Pos-E-Kon
Effective Date:	20111002
Material:	Die-Cast Aluminum Alloy
Product Name:	OTHER PARTS F/EQU IN 8535
Product Type:	Hoods-Standard Mount
Standards:	UL E215386
Surface Finishing:	Epoxy Powder Coated
Temperature Range:	-40 to +257 °F

External Classifications and Standards

ETIM 7:	EC000437 - Housing for rectangular connectors
ETIM 8:	EC000437 - Housing for rectangular connectors
ETIM 9:	EC000437 - Housing for rectangular connectors
ETIM 10:	EC000437 - Housing for rectangular connectors
UNSPSC:	39121424
IDEA Granular Category Code (IGCC):	4594 >> Terminal block covers

Material Compliance

WEEE Category:	Product Not in WEEE Scope
-----------------------	---------------------------

Categories

Products > Low Voltage Products and Systems > Installation Products > Wire Management and Connectivity > Pin & Sleeve Connectors

