



C450
Phase Control SCR
 1460-1640 Amperes/500-1400 Volts

C450
Outline Drawing

| Dimensions | Inches | | Millimeters | |
|------------|--------|--------|-------------|--------|
| | Min. | Max. | Min. | Max. |
| A | 1.020 | 1.065 | 25.90 | 27.05 |
| B | 1.845 | 1.855 | 46.86 | 47.12 |
| C | — | 2.940 | — | 74.68 |
| D | .030 | — | .76 | — |
| E | .050 | — | 1.27 | — |
| F | .017 | .023 | .43 | .58 |
| G | .057 | .059 | 1.44 | 1.50 |
| H | .186 | .191 | 4.72 | 4.85 |
| J | .245 | .255 | 6.22 | 6.48 |
| K | .115 | .130 | 2.92 | 3.30 |
| L | .064 | .070 | 1.62 | 1.78 |
| M | — | 1.800 | — | 45.72 |
| N | — | 2.650 | — | 67.31 |
| P | .135 | .145 | 3.42 | 3.68 |
| Q | .070 | .100 | 1.77 | 2.54 |
| R | — | 1.355 | — | 34.42 |
| S | 12.219 | 12.343 | 310.36 | 313.51 |
| T | .137 | .153 | 3.47 | 3.89 |