

TUFF-SEAL™



**RSPV SERIES VALOX
CORD GRIPS**



**RSPV Series Valox®
Corrosion-Resistant
Cord Connectors**

The Tuff Seal RSPV Series of Non-Metallic Cord Connectors are constructed of Valox for superior corrosion

resistance and are suitable for use in FDA-mandated washdowns. These connectors are ideally suited for use in applications with moisture and they provide an environmental seal against dirt, coolants, fumes and the like.

RSPV Connectors can be ordered with or without wire mesh attachments. The straight-body style accommodates 3/8", 1/2" and 3/4" conduit sizes while the 90° body fits 1/2" and 3/4" conduit. They feature a compression bushing made of high-quality, oil resistant Neoprene rubber with an anti-friction washer made of nylon.

RSPV Connectors are suitable for use in both indoor and outdoor applications to prevent cable pullout and control arc of bend.

NOTES

Cord Grip Accessories

Locknuts: add "-L" to any part number

Special Configurations

Special configurations and materials are available.

Consult factory.

All wire mesh is stainless steel.

Dimension & certification information on pages 44 & 48 in Tuff-Seal Technical Reference.

Valox is registered trademark of GE Plastics

RSPV SERIES-STRAIGHT

COMPLETE ASSEMBLY PART NUMBERS

Conduit Size (NPT)	Cable Range	Cord Grip	Cord Grip With Mesh
3/8"			
	.125 – .188	RSPV-003	RSPV-003-E
	.188 – .250	RSPV-004	RSPV-004-E
	.250 – .312	RSPV-005	RSPV-005-E
	.312 – .375	RSPV-006	RSPV-006-E
	.375 – .438	RSPV-007	RSPV-007-E
1/2"			
	.125 – .188	RSPV-103	RSPV-103-E
	.188 – .250	RSPV-104	RSPV-104-E
	.250 – .312	RSPV-105	RSPV-105-E
	.312 – .375	RSPV-106	RSPV-106-E
	.375 – .438	RSPV-107	RSPV-107-E
	.438 – .500	RSPV-108	RSPV-108-E
	.500 – .562	RSPV-109	RSPV-109-E
	.562 – .625	RSPV-110	RSPV-110-E
3/4"			
	.438 – .500	RSPV-208	RSPV-208-E
	.500 – .562	RSPV-209	RSPV-209-E
	.500 – .625	RSPV-210	RSPV-210-E
	.562 – .688	RSPV-211	RSPV-211-E
	.625 – .750	RSPV-212	RSPV-212-E
	.688 – .812	RSPV-213	RSPV-213-E

RSPV SERIES-90°

COMPLETE ASSEMBLY PART NUMBERS

Conduit Size (NPT)	Cable Range	Cord Grip	Cord Grip With Mesh
1/2"			
	.125 – .188	RSPV-9103	RSPV-9103-E
	.188 – .250	RSPV-9104	RSPV-9104-E
	.250 – .312	RSPV-9105	RSPV-9105-E
	.312 – .375	RSPV-9106	RSPV-9106-E
	.375 – .438	RSPV-9107	RSPV-9107-E
	.438 – .500	RSPV-9108	RSPV-9108-E
	.500 – .562	RSPV-9109	RSPV-9109-E
	.562 – .625	RSPV-9110	RSPV-9110-E
3/4"			
	.500 – .562	RSPV-9209	RSPV-9209-E
	.500 – .625	RSPV-9210	RSPV-9210-E
	.562 – .688	RSPV-9211	RSPV-9211-E
	.625 – .750	RSPV-9212	RSPV-9212-E
	.688 – .812	RSPV-9213	RSPV-9213-E

*Cable may have to be stripped to pass through the bore of the body

