

[> View Items](#)

M8 Attachable Connector

Check up to five results to perform an action.



Remke's family of E-CON Connectors provide the performance required in today's manufacturing environment yet offer a lower installation cost than other M12 connectors on the market.

The E-CON family of industrial interconnects includes both single-ended and double-ended M12 and M8 connectors, cable assemblies, receptacles and attachable connectors. The E-CON line features:

- ε Single and double-ended male and female plugs in straight or 90° configurations
- ε Cost-effective, fast and easy replacement of sensors, switches and control components
- ε IP67 and NEMA6P protection
- ε Nickel-plated brass couplers, 1/4" NPT receptacles and PVC - jacketed type cable
- ε Factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching.

Features of the M12 E-CON Connectors include gold plated contacts, vibration resistance and T-barb design. M8 connectors feature a compact design along with gold plated contacts. Both the M12 and M8 connectors are made with corrosion-resistant materials. And the lower price-point of these connectors makes them ideal for use by price-sensitive OEM's, or in standard industrial applications that don't need a custom solution.

Results1 - 8 of 8

1

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Cable Entry</u>	<u>UPC 785411</u>	
M803EFW7	Male Straight	3	PG7	81507	\$18.20
M804EFW7	Male Straight	4	PG7	81510	\$22.55
M803FFW7	Male 90 Degree	3	PG7	81508	\$18.20
M804FFW7	Male 90 Degree	4	PG7	81511	\$22.55
M803AFW7	Female Straight	3	PG7	81505	\$18.20
M804EFW7	Female Straight	4	PG7	81510	\$22.55
M803CFW7	Female 90 Degree	3	PG7	81506	\$18.20
M804CFW7	Female 90 Degree	4	PG7	81509	\$22.55

Results1 - 8 of 8

1