


> View Items

### M8 E-CON Plug Assembly

Check up to five results to perform an action.



Remke's family of E-CON Connectors provide the performance required in today's manufacturing environment yet offer a lower installation cost than other M12 connectors on the market.



The E-CON family of industrial interconnects includes both single-ended and double-ended M12 and M8 connectors, cable assemblies, receptacles and attachable connectors. The E-CON line features:

- ε Single and double-ended male and female plugs in straight or 90° configurations
- ε Cost-effective, fast and easy replacement of sensors, switches and control components
- ε IP67 and NEMA6P protection
- ε Nickel-plated brass couplers, 1/4" NPT receptacles and PVC - jacketed type cable
- ε Factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching.

Features of the M12 E-CON Connectors include gold plated contacts, vibration resistance and T-barb design. M8 connectors feature a compact design along with gold plated contacts. Both the M12 and M8 connectors are made with corrosion-resistant materials. And the lower price-point of these connectors makes them ideal for use by price-sensitive OEM's, or in standard industrial applications that don't need a custom solution.

Results1 - 16 of 16

1

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Face View</u>	<u>Cable Length</u>	<u>UPC 785411</u>	
<a href="#">PC03A006611E</a>	Female Straight	3	 <a href="#">PC03A006611E</a> <a href="#">larger image</a>	2 M	81512	\$11.85
<a href="#">PC03A009811E</a>	Female Straight	3	 <a href="#">PC03A009811E</a> <a href="#">larger image</a>	3 M	81513	\$13.65

<a href="#">PC03A016411E</a>	Female Straight	3		5 M	81514	\$15.90
			PC03A016411E <a href="#">larger image</a>			
<a href="#">PC03A032811E</a>	Female Straight	3		10 M	81515	\$26.25
			PC03A032811E <a href="#">larger image</a>			
<a href="#">PC04A006611E</a>	Female Straight	4		2 M	81520	\$13.05
			PC04A006611E <a href="#">larger image</a>			
<a href="#">PC04A009811E</a>	Female Straight	4		3 M	81521	\$14.85
			PC04A009811E <a href="#">larger image</a>			
<a href="#">PC04A016411E</a>	Female Straight	4		5 M	81522	\$17.10
			PC04A016411E <a href="#">larger image</a>			
<a href="#">PC04A032811E</a>	Female Straight	4		10 M	81523	\$27.70
			PC04A032811E <a href="#">larger image</a>			
<a href="#">PC03C006611E</a>	Female 90 Degree	3		2 M	81516	\$11.85
			PC03C006611E <a href="#">larger image</a>			

<a href="#">PC03C009811E</a>	Female 90 Degree	3		3 M	81517	\$13.65
			PC03C009811E <a href="#">larger image</a>			
<a href="#">PC03C016411E</a>	Female 90 Degree	3		5 M	81518	\$15.90
			PC03C016411E <a href="#">larger image</a>			
<a href="#">PC03C032811E</a>	Female 90 Degree	3		10 M	81519	\$26.25
			PC03C032811E <a href="#">larger image</a>			
<a href="#">PC04C006611E</a>	Female 90 Degree	4		2 M	81524	\$13.05
			PC04C006611E <a href="#">larger image</a>			
<a href="#">PC04C009811E</a>	Female 90 Degree	4		3 M	81525	\$14.85
			PC04C009811E <a href="#">larger image</a>			
<a href="#">PC04C016411E</a>	Female 90 Degree	4		5 M	81526	\$17.10
			PC04C016411E <a href="#">larger image</a>			
<a href="#">PC04C032811E</a>	Female 90 Degree	4		10 M	81527	\$27.70
			PC04C032811E <a href="#">larger image</a>			