

[> View Items](#)

Dual Key PUR Micro-Link™ Cable Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.
Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :

- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
402K0060K	Male/Female Non-Braided	2		1-Brown 2-Blue	6 ft.	80571	\$27.30
			402K0060K larger image				
402K0120K	Male/Female Non-Braided	2		1-Brown 2-Blue	12 ft.	80574	\$25.30
			402K0120K larger image				
402K0200K	Male/Female Non-Braided	2		1-Brown 2-Blue	20 ft.	80576	\$33.45
			402K0200K larger image				
403K0060K	Male/Female Non-Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80622	\$28.70
			403K0060K larger image				
403K0120K	Male/Female Non-Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80626	\$31.80
			403K0120K larger image				
403K0200K	Male/Female Non-Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80629	\$35.65
			403K0200K larger image				
404K0060K	Male/Female Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80675	\$32.75
			404K0060K larger image				


404K0120K	Male/Female Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80679	\$36.65
			404K0120K larger image				
404K0200K	Male/Female Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80682	\$42.10
			404K0200K larger image				
405K0060K	Male/Female Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80722	\$39.00
			405K0060K larger image				
405K0120K	Male/Female Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80726	\$44.00
			405K0120K larger image				
405K0200K	Male/Female Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80729	\$50.80
			405K0200K larger image				
406K0060K	Male/Female Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80755	\$44.95
			406K0060K larger image				
406K0120K	Male/Female Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80757	\$55.90
			406K0120K larger image				


[406K0200K](#) Male/Female Non-Braided 6  1-Red/White
2-Red
3-Green
4-Red/Yellow
5-Red/Black
6-Red/Blue 20 ft. 80758 \$70.90
406K0200K
[larger image](#)


[402K0060AK](#) Male/Female Braided 2  1-Brown
2-Blue 6 ft. 80569 \$32.90
402K0060AK
[larger image](#)

[402K0120AK](#) Male/Female Braided 2  1-Brown
2-Blue 12 ft. 80572 \$36.50
402K0120AK
[larger image](#)

[402K0200AK](#) Male/Female Braided 2  1-Brown
2-Blue 20 ft. 81464 QUOTE
402K0200AK
[larger image](#)

[403K0060AK](#) Male/Female Braided 3  1-Green
2-Red/Black
3-Red/White 6 ft. 80620 \$29.25
403K0060AK
[larger image](#)

[403K0120AK](#) Male/Female Braided 3  1-Green
2-Red/Black
3-Red/White 12 ft. 80624 \$34.90
403K0120AK
[larger image](#)

[403K0200AK](#) Male/Female Braided 3  1-Green
2-Red/Black
3-Red/White 20 ft. 81465 QUOTE
403K0200AK
[larger image](#)

404K0060AK	Male/Female Braided	4	 404K0060AK larger image	1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80673	\$35.20
404K0120AK	Male/Female Braided	4	 404K0120AK larger image	1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80677	\$43.65
404K0200AK	Male/Female Braided	4	 404K0200AK larger image	1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	81466	QUOTE
405K0060AK	Male/Female Braided	5	 405K0060AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80720	\$40.85
405K0120AK	Male/Female Braided	5	 405K0120AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80724	\$52.75
405K0200AK	Male/Female Braided	5	 405K0200AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	81473	QUOTE

406K0060AK	Male/Female Braided	6	 406K0060AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80754	\$50.00
406K0120AK	Male/Female Braided	6	 406K0120AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80756	\$62.25
406K0200AK	Male/Female Braided	6	 406K0200AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	81474	QUOTE

Results1 - 30 of 30