

[> View Items](#)

Dual Key PUR Micro-Link™ Male Plug Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.
Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :

- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
402E0060K	Straight Plug Non-Braided	2		1-Brown 2-Blue	6 ft.	80553	\$15.05
			402E0060K larger image				
402E0120K	Straight Plug Non-Braided	2		1-Brown 2-Blue	12 ft.	80556	\$17.70
			402E0120K larger image				
402E0200K	Straight Plug Non-Braided	2		1-Brown 2-Blue	20 ft.	80559	\$21.35
			402E0200K larger image				
403E0060K	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80600	\$15.85
			403E0060K larger image				
403E0120K	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80604	\$18.95
			403E0120K larger image				
403E0200K	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80609	\$22.85
			403E0200K larger image				
404E0060K	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80653	\$18.30
			404E0060K larger image				

404E0120K	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80657	\$22.50
			404E0120K larger image				
404E0200K	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80662	\$27.70
			404E0200K larger image				
405E0060K	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80703	\$22.20
			405E0060K larger image				
405E0120K	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80706	\$27.15
			405E0120K larger image				
405E0200K	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80709	\$33.90
			405E0200K larger image				
406E0060K	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80743	\$28.15
			406E0060K larger image				
406E0120K	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80745	\$37.60
			406E0120K larger image				

406E0200K	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80747	\$54.05
			406E0200K larger image				
402E0060AK	Straight Plug Braided	2		1-Brown 2-Blue	6 ft.	80551	\$17.05
			402E0060AK larger image				
402E0120AK	Straight Plug Braided	2		1-Brown 2-Blue	12 ft.	80554	\$20.75
			402E0120AK larger image				
402E0200AK	Straight Plug Braided	2		1-Brown 2-Blue	20 ft.	80557	\$25.45
			402E0200AK larger image				
403E0060AK	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80598	\$17.85
			403E0060AK larger image				
403E0120AK	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80602	\$23.65
			403E0120AK larger image				
403E0200AK	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80607	\$31.10
			403E0200AK larger image				

404E0060AK	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80651	\$22.30
			404E0060AK larger image				
404E0120AK	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80655	\$31.45
			404E0120AK larger image				
404E0200AK	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80660	\$43.50
			404E0200AK larger image				
405E0060AK	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80701	\$27.00
			405E0060AK larger image				
405E0120AK	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80704	\$39.00
			405E0120AK larger image				
405E0200AK	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80707	\$55.10
			405E0200AK larger image				





406E0060AK	Straight Plug Braided	6	 406E0060AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80742	\$31.35
406E0120AK	Straight Plug Braided	6	 406E0120AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80744	\$41.70
406E0200AK	Straight Plug Braided	6	 406E0200AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80746	\$60.00
402F0060K	90° Plug Non-Braided	2	 402F0060K larger image	1-Brown 2-Blue	6 ft.	80562	\$15.05
402F0120K	90° Plug Non-Braided	2	 402F0120K larger image	1-Brown 2-Blue	12 ft.	80565	\$17.70
402F0200K	90° Plug Non-Braided	2	 402F0200K larger image	1-Brown 2-Blue	20 ft.	80568	\$21.35
403F0060K	90° Plug Non-Braided	3	 403F0060K larger image	1-Green 2-Red/Black 3-Red/White	6 ft.	80612	\$15.85

403F0120K	90° Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80615	\$18.95
			403F0120K larger image				
403F0200K	90° Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80618	\$22.85
			403F0200K larger image				
404F0060K	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80665	\$18.30
			404F0060K larger image				
404F0120K	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80668	\$22.50
			404F0120K larger image				
404F0200K	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80671	\$27.70
			404F0200K larger image				
405F0060K	90° Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80712	\$22.20
			405F0060K larger image				
405F0120K	90° Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80715	\$27.15
			405F0120K larger image				

405F0200K	90° Plug Non-Braided	5	 405F0200K larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80718	\$27.15
406F0060K	90° Plug Non-Braided	6	 406F0060K larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80749	\$28.15
406F0120K	90° Plug Non-Braided	6	 406F0120K larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80751	\$37.60
406F0200K	90° Plug Non-Braided	6	 406F0200K larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80753	\$54.05
402F0060AK	90° Plug Braided	2	 402F0060AK larger image	1-Brown 2-Blue	6 ft.	80560	\$17.05
402F0120AK	90° Plug Braided	2	 402F0120AK larger image	1-Brown 2-Blue	12 ft.	80563	\$20.75

402F0200AK	90° Plug Braided	2		1-Brown 2-Blue	20 ft.	80566	\$25.45
			402F0200AK larger image				
403F0060AK	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80610	\$17.85
			403F0060AK larger image				
403F0120AK	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80613	\$23.65
			403F0120AK larger image				
403F0200AK	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80616	\$31.10
			403F0200AK larger image				
404F0060AK	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80663	\$22.30
			404F0060AK larger image				
404F0120AK	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80666	\$31.45
			404F0120AK larger image				
404F0200AK	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80669	\$43.50
			404F0200AK larger image				

405F0060AK	90° Plug Braided	5	 405F0060AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80710	\$27.00
405F0120AK	90° Plug Braided	5	 405F0120AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80713	\$39.00
405F0200AK	90° Plug Braided	5	 405F0200AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80716	\$55.10
406F0060AK	90° Plug Braided	6	 406F0060AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80748	\$31.35
406F0120AK	90° Plug Braided	6	 406F0120AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80750	\$41.70
406F0200AK	90° Plug Braided	6	 406F0200AK larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80752	\$60.00
202S0010P	Mating Female Receptacle	2	 202S0010P larger image	1-Brown 2-Blue	N/A	80209	\$12.10

203S0010P	Mating Female Receptacle	3		1-Green 2-Red/Black 3-Red/White	N/A	80247	\$13.05
			203S0010P larger image				
204S0010P	Mating Female Receptacle	4		1-Red/Black 2-Red/White 3-Red 4-Green	N/A	80287	\$15.85
			204S0010P larger image				
205S0010P	Mating Female Receptacle	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	N/A	80325	\$16.00
			205S0010P larger image				
206S0010P	Mating Female Receptacle	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	N/A	80360	\$17.75
			206S0010P larger image				