

[> View Items](#)

Single Key (M12) PUR Micro-Link™ Cable Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.

Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :

- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
503K0066L	Male/Female Non-Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	2 M	80804	\$29.90
			503K0066L larger image				
503K0131L	Male/Female Non-Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	4 M	80808	\$33.00
			503K0131L larger image				
503K0164L	Male/Female Non-Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	5 M	80812	\$41.55
			503K0164L larger image				
504K0066L	Male/Female Non-Braided	4		1-Brown 2-White 3-Blue 4-Black	2 M	80858	\$38.80
			504K0066L larger image				
504K0131L	Male/Female Non-Braided	4		1-Brown 2-White 3-Blue 4-Black	4 M	80862	\$48.60
			504K0131L larger image				
504K0164L	Male/Female Non-Braided	4		1-Brown 2-White 3-Blue 4-Black	5 M	80866	\$39.00
			504K0164L larger image				
505K0066L	Male/Female Non-Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	2 M	80912	\$40.70
			505K0066L larger image				

505K0131L	Male/Female Non-Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	4 M	80916	\$46.10
			505K0131L larger image				
505K0164L	Male/Female Non-Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	5 M	80920	\$48.75
			505K0164L larger image				
503K0066AL	Male/Female Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	2 M	80802	\$31.55
			503K0066AL larger image				
503K0131AL	Male/Female Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	4 M	80806	\$39.00
			503K0131AL larger image				
503K0164AL	Male/Female Braided	3		1-Brown 2-Not Used 3-Blue 4-Black	5 M	80810	\$42.60
			503K0164AL larger image				
504K0066AL	Male/Female Braided	4		1-Brown 2-White 3-Blue 4-Black	2 M	80856	\$35.05
			504K0066AL larger image				
504K0131AL	Male/Female Braided	4		1-Brown 2-White 3-Blue 4-Black	4 M	80860	\$44.60
			504K0131AL larger image				

504K0164AL	Male/Female Braided	4		1-Brown 2-White 3-Blue 4-Black	5 M	80864	\$49.55
			504K0164AL larger image				
505K0066AL	Male/Female Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	2 M	80910	\$43.75
			505K0066AL larger image				
505K0131AL	Male/Female Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	4 M	80914	\$55.90
			505K0131AL larger image				
505K0164AL	Male/Female Braided	5		1-Brown 2-White 3-Blue 4-Black 5-Gray	5 M	80918	\$61.85
			505K0164AL larger image				