

[> View Items](#)

Dual Key PVC Micro-link™ Male Plug Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.
Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :

- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
202E0060T	Straight Plug Non-Braided	2		1-Brown 2-Blue	6 ft.	80188	\$15.70
			202E0060T larger image				
202E0120T	Straight Plug Non-Braided	2		1-Brown 2-Blue	12 ft.	80190	\$18.40
			202E0120T larger image				
202E0200T	Straight Plug Non-Braided	2		1-Brown 2-Blue	20 ft.	80192	\$22.20
			202E0200T larger image				
203E0060T	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80224	\$16.55
			203E0060T larger image				
203E0120T	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80226	\$19.65
			203E0120T larger image				
203E0200T	Straight Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80228	\$23.80
			203E0200T larger image				
204E0060T	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80263	\$19.20
			204E0060T larger image				







204E0120T	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80265	\$22.45
			204E0120T larger image				
204E0200T	Straight Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80267	\$28.90
			204E0200T larger image				
205E0060T	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80303	\$23.00
			205E0060T larger image				
205E0120T	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80305	\$28.30
			205E0120T larger image				
205E0200T	Straight Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80307	\$35.35
			205E0200T larger image				
206E0060T	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80341	\$29.35
			206E0060T larger image				
206E0120T	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80343	\$39.00
			206E0120T larger image				

206E0200T	Straight Plug Non-Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80345	\$56.25
			206E0200T larger image				
202E0060G	Straight Plug Braided	2		1-Brown 2-Blue	6 ft.	80187	\$17.80
			202E0060G larger image				
202E0120G	Straight Plug Braided	2		1-Brown 2-Blue	12 ft.	80189	\$21.55
			202E0120G larger image				
202E0200G	Straight Plug Braided	2		1-Brown 2-Blue	20 ft.	80191	\$26.50
			202E0200G larger image				
203E0060G	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80223	\$18.45
			203E0060G larger image				
203E0120G	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80225	\$24.50
			203E0120G larger image				
203E0200G	Straight Plug Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80227	\$32.40
			203E0200G larger image				

204E0060G	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80262	\$23.15
			204E0060G larger image				
204E0120G	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80264	\$32.75
			204E0120G larger image				
204E0200G	Straight Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80266	\$45.50
			204E0200G larger image				
205E0060G	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80302	\$28.05
			205E0060G larger image				
205E0120G	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80304	\$40.55
			205E0120G larger image				
205E0200G	Straight Plug Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80306	\$57.45
			205E0200G larger image				

206E0060G	Straight Plug Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80340	\$32.60
			206E0060G larger image				
206E0120G	Straight Plug Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80342	\$43.40
			206E0120G larger image				
206E0200G	Straight Plug Braided	6		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80344	\$62.50
			206E0200G larger image				
202F0060T	90° Plug Non-Braided	2		1-Brown 2-Blue	6 ft.	80194	\$15.70
			202F0060T larger image				
202F0120T	90° Plug Non-Braided	2		1-Brown 2-Blue	12 ft.	80196	\$18.40
			202F0120T larger image				
202F0200T	90° Plug Non-Braided	2		1-Brown 2-Blue	20 ft.	80198	\$22.20
			202F0200T larger image				
203F0060T	90° Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80230	\$16.55
			203F0060T larger image				

203F0120T	90° Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80233	\$19.65
			203F0120T larger image				
203F0200T	90° Plug Non-Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80235	\$23.80
			203F0200T larger image				
204F0060T	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80269	\$19.20
			204F0060T larger image				
204F0120T	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80271	\$23.35
			204F0120T larger image				
204F0200T	90° Plug Non-Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80273	\$28.90
			204F0200T larger image				
205F0060T	90° Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80309	\$23.00
			205F0060T larger image				
205F0120T	90° Plug Non-Braided	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80311	\$28.30
			205F0120T larger image				

205F0200T	90° Plug Non-Braided	5	 <p>205F0200T larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80313	\$35.35
206F0060T	90° Plug Non-Braided	6	 <p>206F0060T larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80347	\$29.35
206F0120T	90° Plug Non-Braided	6	 <p>206F0120T larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80349	\$39.00
206F0200T	90° Plug Non-Braided	6	 <p>206F0200T larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80351	\$56.25
202F0060G	90° Plug Braided	2	 <p>202F0060G larger image</p>	1-Brown 2-Blue	6 ft.	80193	\$17.05
202F0120G	90° Plug Braided	2	 <p>202F0120G larger image</p>	1-Brown 2-Blue	12 ft.	80195	\$21.55

202F0200G	90° Plug Braided	2		1-Brown 2-Blue	20 ft.	80197	\$26.50
			202F0200G larger image				
203F0060G	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80229	\$18.45
			203F0060G larger image				
203F0120G	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80232	\$24.50
			203F0120G larger image				
203F0200G	90° Plug Braided	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80234	\$32.40
			203F0200G larger image				
204F0060G	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80268	\$23.15
			204F0060G larger image				
204F0120G	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80270	\$32.75
			204F0120G larger image				
204F0200G	90° Plug Braided	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80272	\$45.50
			204F0200G larger image				

205F0060G	90° Plug Braided	5	 205F0060G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80308	\$28.05
205F0120G	90° Plug Braided	5	 205F0120G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80310	\$40.55
205F0200G	90° Plug Braided	5	 205F0200G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80312	\$57.45
206F0060G	90° Plug Braided	6	 206F0060G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	6 ft.	80346	\$32.60
206F0120G	90° Plug Braided	6	 206F0120G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	12 ft.	80348	\$43.40
206F0200G	90° Plug Braided	6	 206F0200G larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	20 ft.	80350	\$62.50
202S0010P	Mating Male Receptacle	2	 202S0010P larger image	1-Brown 2-Blue	6 ft.	80209	\$12.10

203S0010P	Mating Male Receptacle	3	 <p>203S0010P larger image</p>	1-Green 2-Red/Black 3-Red/White	N/A	80247	\$13.05
204S0010P	Mating Male Receptacle	4	 <p>204S0010P larger image</p>	1-Red/Black 2-Red/White 3-Red 4-Green	N/A	80287	\$15.85
205S0010P	Mating Male Receptacle	5	 <p>205S0010P larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	N/A	80325	\$16.00
206S0010P	Mating Male Receptacle	6	 <p>206S0010P larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black 6-Red/Blue	N/A	80360	\$17.75