



RSRS SERIES STEEL CORD GRIPS



RSRS SERIES STEEL CORD CONNECTORS

The Tuff-Seal™ RSRS series of corrosion-resistant cord connectors features a body and compression nut made of zinc-chromium plated steel for added strength and durability, enhanced resistance to rust and a better physical appearance. These connectors are ideally suited for use in washdowns or high moisture environments in food processing plants, petrochemical facilities, wastewater treatment plants, pulp & paper mills and chemical manufacturing factories.

RSRS cord connectors have been designed to withstand the extremes of water, caustic materials, detergents or surfactants.

RSRS Corrosion-Resistant Connectors can be ordered with or without wire mesh and accommodate 3/8", 1/2", 3/4" and 1" conduit. The combination tightening surface on these connectors is a unique Remke design that provides a large wrenching area for easy installation. And the knurl section offers users an extra gripping surface for initial hand tightening.

NOTES

CORD GRIP ACCESSORIES

Locknuts: add "-L" to any part number
O-Rings: add "-R" to any part number

SPECIAL CONFIGURATIONS

Special configurations and materials are available. Consult factory.

All wire mesh is stainless steel.

Dimension & certification information on pages 62 & 64 in Tuff-Seal Technical Reference. Dimensions are the same as those for RSR Straight Cord Grips.

COMPLETE ASSEMBLY PART NUMBERS

RSRS SERIES STEEL CORD GRIPS

Conduit Size (NPT)	Cable Range	Cord Grip	Cord Grip With Mesh	
3/8"	.125 – .188	RSRS-003	**	
	.188 – .250	RSRS-004	RSRS-004-E	
	.250 – .312	RSRS-005	RSRS-005-E	
	.312 – .375	RSRS-006	RSRS-006-E	
	.375 – .438	RSRS-007	RSRS-007-E	
1/2"	.125 – .188	RSRS-103	**	
	.188 – .250	RSRS-104	RSRS-104-E	
	.250 – .312	RSRS-105	RSRS-105-E	
	.312 – .375	RSRS-106	RSRS-106-E	
	.375 – .438	RSRS-107	RSRS-107-E	
	.438 – .500	RSRS-108	RSRS-108-E	
	.500 – .562	RSRS-109	RSRS-109-E	
	.562 – .625	RSRS-110	RSRS-110-E	
	3/4"	.438 – .500	RSRS-208	RSRS-208-E
		.500 – .562	RSRS-209	RSRS-209-E
.562 – .625		RSRS-210	RSRS-210-E	
.562 – .688		RSRS-211	RSRS-211-E	
.625 – .750		RSRS-212	RSRS-212-E	
.688 – .812		RSRS-213*	RSRS-213-E	
1"	.500 – .562	RSRS-309	RSRS-309-E	
	.562 – .625	RSRS-310	RSRS-310-E	
	.562 – .688	RSRS-311	RSRS-311-E	
	.625 – .750	RSRS-312	RSRS-312-E	
	.688 – .812	RSRS-313	RSRS-313-E	
	.750 – .875	RSRS-314	RSRS-314-E	
	.812 – .938	RSRS-315	RSRS-315-E	
	.875 – 1.000	RSRS-316	RSRS-316-E	
1 1/4"	.950 – 1.050	RSRS-416	RSRS-416-E	
	1.050 – 1.150	RSRS-418	RSRS-418-E	
	1.150 – 1.250	RSRS-420	RSRS-420-E	
	1.250 – 1.375	RSRS-422	RSRS-422-E	
1 1/2"	.950 – 1.050	RSRS-516	RSRS-516-E	
	1.050 – 1.150	RSRS-518	RSRS-518-E	
	1.150 – 1.250	RSRS-520	RSRS-520-E	
	1.250 – 1.375	RSRS-522	RSRS-522-E	

*Cable may have to be stripped to pass through the bore of the body

**Contact Remke for mesh availability of this part number



CORD CONNECTORS

WIRE MESH GRIPS

PICO-LINK

MICRO-LINK

ETHERLINK

MINI-LINK

MULTI-PORT BOXES

BUS SYSTEM PRODUCTS

