



# 9 TO 12 POLE RUBBER MINI-LINK™ ASSEMBLIES

SPECIFICATIONS			
MATERIALS		ENVIRONMENTAL	
Body	Rubber	Protection	IP 67
Contact	Brass, Gold Plated over Nickel	Operating Temp	-20°C to 90°C
Sleeve	Stainless Steel	CERTIFICATIONS	
Coupling Nut	Machined Aluminum, Black Anodized (stainless steel available)		Recognized, File No. E165657
Cable	#16 AWG NBR/PVC Rubber 65 x #34 stranding 90° C, UL Recognized SOOW, CSA Certified		Certified, File No. E165657
Cable Diameters	9/C-.62", 10/C-.63", 12/C-.67"	OPTIONS	
ELECTRICAL			
Voltage Rating	600 V	Stainless Steel Hardware can be specified - add "1" after Part Number.	
Contact Resistance	≤5mΩ	Consult the factory for custom cord lengths, and a full range of wire management product accessories.	
NOTE			
Not available in #18 AWG.			

## PLUGS AND CABLE ASSEMBLIES WITH #16 AWG SOOW-A CABLE

PLUG ASSEMBLY PART NUMBERS									
Number of Poles	Male Face View	Female Face View	Wiring Color Code	AMP RTG. @ 600V	Cable Length	Male Straight	Female Straight	Female 90°	Male/Female Assembly
9			1-Orange 2-Blue 3-Red-Blk. Tr. 4-Green-Blk. Tr. 5-White 6-Red 7-Green 8-White-Blk. Tr. 9-Black	7A	3 FT	109B0030A	109A0030A	109C0030A	109G0030A
				7A	6 FT	109B0060A	109A0060A	109C0060A	109G0060A
				7A	12 FT	109B0120A	109A0120A	109C0120A	109G0120A
				7A	20 FT	109B0200A	109A0200A	109C0200A	109G0200A
10			1-Orange 2-Blue 3-White-Blk. Tr. 4-Red-Blk. Tr. 5-Green-Blk. Tr. 6-Org.-Blk. Tr. 7-Red 8-Green 9-Black 10-White	7A	3 FT	110B0030A	110A0030A	110C0030A	110G0030A
				7A	6 FT	110B0060A	110A0060A	110C0060A	110G0060A
				7A	12 FT	110B0120A	110A0120A	110C0120A	110G0120A
				7A	20 FT	110B0200A	110A0200A	110C0200A	110G0200A
12			1-Orange 2-Blue 3-Wht.blk. Tr. 4-Red-Blk. Tr. 5-Green-Blk. Tr. 6-Org.-Blk. Tr. 7-Blue.-Blk. Tr. 8-Blk.-Wht. Tr. 9-Green 10-Red 11-White 12-Black	5A	3 FT	112B0030A	112A0030A	112C0030A	112G0030A
				5A	6 FT	112B0060A	112A0060A	112C0060A	112G0060A
				5A	12 FT	112B0120A	112A0120A	112C0120A	112G0120A
				5A	20 FT	112B0200A	112A0200A	112C0200A	112G0200A

