

[> View Items](#)

Dual Key SJOOW Micro-Link™ Male Plug Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.
Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :








- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
602E0060C	Straight Plug	2		1-Brown 2-Blue	6 ft.	81147	\$23.90
			602E0060C larger image				
602E0120C	Straight Plug	2		1-Brown 2-Blue	12 ft.	81148	\$29.80
			602E0120C larger image				
602E0200C	Straight Plug	2		1-Brown 2-Blue	20 ft.	81149	\$37.70
			602E0200C larger image				
603E0060C	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	6 ft.	81162	\$26.25
			603E0060C larger image				
603E0120C	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	12 ft.	81163	\$34.30
			603E0120C larger image				
603E0200C	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	20 ft.	81164	\$44.95
			603E0200C larger image				
604E0060C	Straight Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	81177	\$34.15
			604E0060C larger image				

604E0120C	Straight Plug	4	 <p>604E0120C larger image</p>	1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	81178	\$46.00
604E0200C	Straight Plug	4	 <p>604E0200C larger image</p>	1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	81179	\$61.80
605E0060C	Straight Plug	5	 <p>605E0060C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	81194	\$40.70
605E0120C	Straight Plug	5	 <p>605E0120C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	81195	\$56.40
605E0200C	Straight Plug	5	 <p>605E0200C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	81196	\$77.35
602F0060C	90° Plug	2	 <p>602F0060C larger image</p>	1-Brown 2-Blue	6 ft.	81150	\$23.90
602F0120C	90° Plug	2	 <p>602F0120C larger image</p>	1-Brown 2-Blue	12 ft.	81151	\$29.80

602F0200C	90° Plug	2		1-Brown 2-Blue	20 ft.	81152	\$37.70
			602F0200C larger image				
603F0060C	90° Plug	3		1-Green 2-Red/Black 3-Red/White	6 ft.	81165	\$26.25
			603F0060C larger image				
603F0120C	90° Plug	3		1-Green 2-Red/Black 3-Red/White	12 ft.	81166	\$34.30
			603F0120C larger image				
603F0200C	90° Plug	3		1-Green 2-Red/Black 3-Red/White	20 ft.	81167	\$44.95
			603F0200C larger image				
604F0060C	90° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	81180	\$34.15
			604F0060C larger image				
604F0120C	90° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	81182	\$46.00
			604F0120C larger image				
604F0200C	90° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	81183	\$61.80
			604F0200C larger image				

605F0060C	90° Plug	5	 <p>605F0060C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	81198	\$40.70
605F0120C	90° Plug	5	 <p>605F0120C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	81199	\$56.40
605F0200C	90° Plug	5	 <p>605F0200C larger image</p>	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	81200	\$77.35
202S0010N	Mating Male Receptacle	2	 <p>202S0010N larger image</p>	1-Brown 2-Blue	N/A	80208	\$12.60
203S0010N	Mating Male Receptacle	3	 <p>203S0010N larger image</p>	1-Green 2-Red/Black 3-Red/White	N/A	80246	\$13.05
204S0010N	Mating Male Receptacle	4	 <p>204S0010N larger image</p>	1-Red/Black 2-Red/White 3-Red 4-Green	N/A	80286	\$15.85

[205S0010N](#)

Mating Male
Receptacle

5



205S0010N
[larger image](#)

1-Red/White
2-Red
3-Green
4-Red/Yellow
5-Red/Black

N/A

80324

\$16.00