


> View Items

Dual Key TPE Micro-Link™ Female Plug Assemblies

Check up to five results to perform an action.



Micro-Link™ Interconnects, Cable Assemblies & Receptacles.
Remke's family of Micro-Link (M12) Industrial Interconnects and cordsets includes :

- ε Offering all Micro-Link connectors in four different materials - PVC, PUR, TPE and rubber - to protect against numerous environmental and temperature concerns.
- ε A Shielded Connector that features a 360° aluminum mylar foil shield to minimize electrical interference that tends to disrupt the signal to the control device.

Micro-Link interconnects have been designed for low amperage AC or DC control systems and are compatible with the pin configurations used by major U.S. and European sensor manufacturers.

The Micro-Link family of connectors, cable assemblies and receptacles allow fast and easy replacement of 12mm to 18mm sensors, switches and control components.

These connectors also :








- ε Provide NEMA 6P and IP 68 protection for enhanced moisture resistance
- ε Feature factory molded-to-the-cable construction for durability
- ε Mechanically keyed to eliminate mismatching
- ε Available in 2-6 pole male and female plugs, straight or 90° configurations, single or dual keyway design with optional LED's and cable with or without braiding.

Another important design feature of Remke's Micro-Link Connector are the 'Ribs' - which are molded into the exterior housing to increase the grip-surface thus reducing the chance for slip-off's or the need for disconnection tools. This design feature reduces maintenance and replacement costs.

These connectors are a UL Recognized Component and are ROHS Compliant.

<u>Item #</u>	<u>Item Name</u>	<u>No. of Poles</u>	<u>Contact Rotation</u>	<u>Wiring Color Code</u>	<u>Length</u>	<u>UPC 785411</u>	
402A0060AQ	Straight Plug	2		1-Brown 2-Blue	6 ft.	80534	\$17.05
			402A0060AQ larger image				
402A0120AQ	Straight Plug	2		1-Brown 2-Blue	12 ft.	80537	\$20.75
			402A0120AQ larger image				
402A0200AQ	Straight Plug	2		1-Brown 2-Blue	20 ft.	80540	\$25.45
			402A0200AQ larger image				
403A0060AQ	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80578	\$17.85
			403A0060AQ larger image				
403A0120AQ	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80582	\$23.65
			403A0120AQ larger image				
403A0200AQ	Straight Plug	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80587	\$31.10
			403A0200AQ larger image				
404A0060AQ	Straight Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80631	\$22.30
			404A0060AQ larger image				

404A0120AQ	Straight Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80635	\$31.45
			404A0120AQ larger image				
404A0200AQ	Straight Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80640	\$43.50
			404A0200AQ larger image				
405A0060AQ	Straight Plug	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80684	\$27.00
			405A0060AQ larger image				
405A0120AQ	Straight Plug	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80687	\$39.00
			405A0120AQ larger image				
405A0200AQ	Straight Plug	5		1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80690	\$55.10
			405A0200AQ larger image				
402C0060AQ	90 ° Plug	2		1-Brown 2-Blue	6 ft.	80543	\$17.05
			402C0060AQ larger image				
402C0120AQ	90 ° Plug	2		1-Brown 2-Blue	12 ft.	80546	\$20.75
			402C0120AQ larger image				

402C0200AQ	90 ° Plug	2		1-Brown 2-Blue	20 ft.	80549	\$25.45
			402C0200AQ larger image				
403C0060AQ	90 ° Plug	3		1-Green 2-Red/Black 3-Red/White	6 ft.	80590	\$17.85
			403C0060AQ larger image				
403C0120AQ	90 ° Plug	3		1-Green 2-Red/Black 3-Red/White	12 ft.	80593	\$23.65
			403C0120AQ larger image				
403C0200AQ	90 ° Plug	3		1-Green 2-Red/Black 3-Red/White	20 ft.	80596	\$31.10
			403C0200AQ larger image				
404C0060AQ	90 ° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	6 ft.	80643	\$22.30
			404C0060AQ larger image				
404C0120AQ	90 ° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	12 ft.	80646	\$31.45
			404C0120AQ larger image				
404C0200AQ	90 ° Plug	4		1-Red/Black 2-Red/White 3-Red 4-Green	20 ft.	80649	\$43.50
			404C0200AQ larger image				

405C0060AQ	90 ° Plug	5	 405C0060AQ larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	6 ft.	80693	\$27.00
405C0120AQ	90 ° Plug	5	 405C0120AQ larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	12 ft.	80696	\$39.00
405C0200AQ	90 ° Plug	5	 405C0200AQ larger image	1-Red/White 2-Red 3-Green 4-Red/Yellow 5-Red/Black	20 ft.	80699	\$58.95
202P0010N	Mating Male Receptacle	2	 202P0010N larger image	1-Brown 2-Blue	N/A	80205	\$11.70
203P0010N	Mating Male Receptacle	3	 203P0010N larger image	1-Green 2-Red/Black 3-Red/White	N/A	80242	\$12.15
204P0010N	Mating Male Receptacle	4	 204P0010N larger image	1-Red/Black 2-Red/White 3-Red 4-Green	N/A	80282	\$13.60

[205P0010N](#)

Mating Male
Receptacle

5



205P0010N
[larger image](#)

1-Red/White
2-Red
3-Green
4-Red/Yellow
5-Red/Black

N/A

80320

\$15.00