



NICKEL PLATING OPTIONAL

PART NUMBER	SEALING RANGE	BODY BORE
RSR-103	.125 - .188	.610
RSR-104	.188 - .250	.610
RSR-105	.250 - .312	.610
RSR-106	.312 - .375	.610
RSR-107	.375 - .438	.610
RSR-108	.438 - .500	.610
RSR-109	.500 - .562	.610
RSR-110	.562 - .625	.610

ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-100-B	BODY	ALUMINUM	1
2	SRB-103 THRU SRB-110	BUSHING	NEOPRENE	1
3	SW-100	WASHER	C.R.S. ZINC PLATED	1
4	RSR-100-N	NUT	ALUMINIUM	1
5	LN-50	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE	
A	4/22/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005	DRAWN JCN	4/13	TITLE: RSR-100 SERIES	
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED		SIZE A	DWG. NO. RSR-100 ASSEMBLY
			MATERIAL ALUMINUM	ENG APPR.			
			FINISH	MFG APPR.		SCALE: 2:1	
			DO NOT SCALE DRAWING	Q A.		SHEET 1 OF 1	
				PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.			

5

4

3

2

1