

ABB IEC 60 309 International Pin and Sleeve

Mechanical Interlocks IP67 Rated (Watertight)



Russellstoll® Pin and Sleeve Power Connectors

	POLES & WIRES	VOLTAGE (VAC)	CLOCK HOUR	SWITCHED	FUSED	BREAKERED	MATING PLUG
20 Amp	2P3W	200–250	6h	ABB320MI6W	N/A	N/A	ABB320P6W
	2P3W	480	7h	ABB320MI7W	N/A	N/A	ABB320P7W
	3P4W	125/250	12h	ABB420MI12W	ABB420MF12W	N/A	ABB420P12W
	3P4W	3Ø 200–250	9h	ABB420MI9W	ABB420MF9W	N/A	ABB420P9W
	3P4W	3Ø 480	7h	ABB420MI7W	ABB420MF7W	N/A	ABB420P7W
	3P4W	3Ø 600	5h	ABB420MI5W	ABB420MF5W	N/A	ABB420P5W
	4P5W	3ØY 120/208–144/250	9h	ABB520MI9W	N/A	N/A	ABB520P9W
	4P5W	3ØY 277/480	7h	ABB520MI7W	N/A	N/A	ABB520P7W
	4P5W	3ØY 347/600	5h	ABB520MI5W	N/A	N/A	ABB520P5W
30 Amp	2P3W	100–130	4h	ABB330MI4W	N/A	N/A	ABB330P4W
	2P3W	200–250	6h	ABB330MI6W	N/A	N/A	ABB330P6W
	2P3W	480	7h	ABB330MI7W	N/A	N/A	ABB330P7W
	3P4W	125/250	12h	ABB430MI12W	ABB430MF12W	N/A	ABB430P12W
	3P4W	3Ø 200–250	9h	ABB430MI9W	ABB430MF9W	N/A	ABB430P9W
	3P4W	3Ø 480	7h	ABB430MI7W	ABB430MF7W	N/A	ABB430P7W
	3P4W	3Ø 600	5h	ABB430MI5W	ABB430MF5W	N/A	ABB430P5W
	4P5W	3ØY 120/208–144/250	9h	ABB530MI9W	N/A	N/A	ABB530P9W
	4P5W	3ØY 277/480	7h	ABB530MI7W	ABB530MF7W	N/A	ABB530P7W
4P5W	3ØY 347/600	5h	ABB530MI5W	ABB530MF5W	N/A	ABB530P5W	
32 Amp	3P4W	380 50 Hz/440 60 Hz	3h	ABB432MI3W	N/A	N/A	ABB332P3W
60 Amp	2P3W	100–130	4h	ABB360MI4W	N/A	N/A	ABB360P4W
	2P3W	200–250	6h	ABB360MI6W	ABB360MF6W	N/A	ABB360P6W
	2P3W	480	7h	ABB360MI7W	N/A	N/A	ABB360P7W
	3P4W	125/250	12h	ABB460MI12W	ABB460MF12W	N/A	ABB460P12W
	3P4W	3Ø 200–250	9h	ABB460MI9W	ABB460MF9W	N/A	ABB460P9W
	3P4W	3Ø 480	7h	ABB460MI7W	ABB460MF7W	N/A	ABB460P7W
	3P4W	3Ø 600	5h	ABB460MI5W	ABB460MF5W	N/A	ABB460P5W
	4P5W	3ØY 120/208–144/250	9h	ABB560MI9W	ABB560MF9W	N/A	ABB560P9W
	4P5W	3ØY 277/480	7h	ABB560MI7W	N/A	N/A	ABB560P7W
4P5W	3ØY 347/600	5h	ABB560MI5W	N/A	N/A	ABB560P5W	
100 Amp	2P3W	100–130	4h	ABB3100MI4W	N/A	N/A	ABB3100P4W
	2P3W	200–250	6h	ABB3100MI6W	N/A	N/A	ABB3100P6W
	2P3W	480	7h	ABB3100MI7W	N/A	N/A	ABB3100P7W
	3P4W	125/250	12h	ABB4100MI12W	N/A	ABB4100MB12W	ABB4100P12W
	3P4W	3Ø 200–250	9h	ABB4100MI9W	N/A	ABB4100MB9W	ABB4100P9W
	3P4W	3Ø 480	7h	ABB4100MI7W	N/A	ABB4100MB7W	ABB4100P7W
	3P4W	3Ø 600	5h	ABB4100MI5W	N/A	N/A	ABB4100P5W
	4P5W	3ØY 120/208–144/250	9h	ABB5100MI9W	N/A	ABB5100MB9W	ABB5100P9W
	4P5W	3ØY 277/480	7h	ABB5100MI7W	N/A	ABB5100MB7W	ABB5100P7W