

DuraGard® Waterproof Connections

60 Amp Standard Service



Male Plug

Female Connector

Device Ratings and Polarizations

Maximum 600VAC or 250VDC

POLE	WIRE	SAFETY POLARIZATION (RECEPTACLE)	VOLTAGE	CAT. NO. <input type="checkbox"/>	CAT. NO. <input type="checkbox"/>
2	3		125VAC	9P63U1	9C63U1
			250VAC	9P63U2	9C63U2
3	4		125/250VAC	9P64U1	9C64U1
			3Ø 250VAC	9P64U2	9C64U2

Add suffix — / xxxx for bushing I.D. (page 65) or conduit adapter assembled.

◆ "W" suffix is watertight; "F" suffix for splash-proof spring flap cover.

60 Amp Reverse Service



Female Receptacle

Female Plug

Male Receptacle

STANDARD BUSHING I.D.: PLUG/CONN.*	CAT. NO. <input type="checkbox"/>	CAT. NO. <input type="checkbox"/>	CAT. NO. <input type="checkbox"/>
Standard 1.000"; for optional size, see page 65	9R63U1	9F63U1	9B63U1
	9R63U2	9F63U2	9B63U2
Standard 1.000"; for optional size, see page 65	9R64U1	9F64U1	9B64U1
	9R64U2	9F64U2	9B64U2

Add suffix — / xxxx for bushing I.D. (page 65) or conduit adapter assembled.

◆ "W" suffix is watertight; "F" suffix for splash-proof spring flap cover.

* Consult Technical Services.