

30–200/270 Amp (30–200A Load Breaking), Maximum 600VAC/250VDC  
Load-Breaking Receptacles, Plugs, Connectors and Inlets

### Receptacle Mounting Options — J-Line Construction

Progressive Assembly

Mounting Style	To Order Use:	Current Rating			
		30 Amp	60 Amp	100/150 Amp	200/270 Amp
Standard Series JRFA/JRSA □  	Receptacle + Vertical or Square Mount Box + Angle Adapter	Basic Receptacle* + JB3-B100 1" Std. Conduit Size + JAA3 (20°) or JAA3-45 (45°)	Basic Receptacle* + JB6-B150 1d" Std. Conduit Size + JAA6-AB6 (20°) or JAA6-45 (45°)	Basic Receptacle* + JB10-B200 2" Std. Conduit Size + JAA10 (20°) or JAA10-45 (45°)	Basic Receptacle* + JB20 3" Std. Conduit Size + JAA20 (20°) or JAA20-45 (45°)
Series JRFR/JRSR □ Straight  	Receptacle + Vertical Mount Box + Straight Adapter	Basic Receptacle* + JB3-B100 1" Std. Conduit Size + JRA3	Basic Receptacle* + JB6-B150 1½" Std. Conduit Size + JRA6-AB6	Basic Receptacle* + JB10-B200 2" Std. Conduit Size + JRA10	Basic Receptacle* + JB20 3" Std. Conduit Size + JRA20
Series JRFB/JRSB □  	Receptacle + 30° Angle Adapter	Basic Receptacle* + JAAB3	Basic Receptacle* + JAAB6	Basic Receptacle* + JAAB10	Basic Receptacle* + JAAB20
Series JRFE/JRSE □  	Receptacle + Angle Enclosure	Basic Receptacle* + JE3 1" Std. Conduit Size	Basic Receptacle* + JE6 1½" Std. Conduit Size	Basic Receptacle* + JE10 2" Std. Conduit Size	N/A
Series JRFH/JRSH □ Horizontal  	Receptacle + Horizontal Mount Box + Angle Adapter	Basic Receptacle* + JB3-B100 1" Std. Conduit Size + JHA3 (20°)	N/A	N/A	N/A

\* Select appropriate receptacle by rating, configuration and voltage on page 59.

□ NOTE: JRXX 3rd letter denotes Flap (F) or Screw (S) Cover.

Ex: JRSA — Screw Cover

JRFA — Flap Cover

JRF — Flap Cover, Basic Receptacle

JRS — Screw Cover, Basic Receptacle