







## Mipco™ Connections for Refrigerated Containers

### Reversed Contacts Service — 30A and 50A, 250VAC

Power & High Voltage — Russellstoll® Pin & Sleeve Power Connectors

#### Female Plugs

#### Male Connectors and Receptacles

CAT. NO.	DIMENSIONS	RATING	CAT. NO.	DIMENSIONS
334FP•		<b>30 AMP</b> <b>250VAC,</b> 60 Hz 3P4W	334MC ▲	
			334MR ▲	
534FP•		<b>50 AMP</b> <b>250VAC,</b> 60 Hz 3P4W	534MC ▲	
			534MR ▲	

Note: Many additional bushing sizes available; see page H-478.

- Polycarbonate housing.
- ▲ DuraV® housing, UL94V-0 flame rated.
- ★ AMTUF® housing.