

Mipco™ Connections for Refrigerated Containers

Fixed Receptacles with Monitor Switches

These receptacles include a micro switch mounted at the rear of the interior. The switch is mechanically activated by plug (ground pin) insertion. Applications include electrical interlocking, control circuits and safe switch or monitor systems. (Micro switch is a separate circuit.)

CAT. NO.	DIMENSIONS	RATING	
3334FRVSMS▲*		32 AMP 380/440VAC 50/60 Hz, 3P4W IEC309-2 480VAC USA	
6234FRMS*★		60 AMP 250VAC 60 Hz 3P4W	

* Flap Cap also available.

Polycarbonate housing used on 6234FRMS.

▲ DuraV® housing used for 3334FRVSMS; replaces 3334FRPSMS.

★ AMTUF® housing.

Power & High Voltage — Russellstoll® Pin & Sleeve Power Connectors

Special Rated Plugs and Connectors

20 Amp and Australian

CAT. NO.	DIMENSIONS	RATING	CAT. NO.	DIMENSIONS
Male Plugs			Female Connectors	
223MP2		20 AMP 250VAC, 60 Hz 2P3W	223FC2	
334MP5		32 AMP Australian Standard 440/500 VAC, 50 Hz 3P4W	334FC5	