



Waterproof Polycarbonate Enclosures

PART NUMBER	OVERALL H x W x D	INSIDE A x B x C	MOUNTING VER. E x F	J	K	L	M	N	UNIT WT.	PANEL
EP060605-O	7.41 x 8.68 x 5.84	5.94 x 5.94 x 5.02	8.04 x 3.64	4.50	4.25	4.25	8.89	8.89	2.5	BP★0606*
EP060605-T	(188 x 223 x 148)	(151 x 151 x 127)	(204 x 92)	(114)	(108)	(108)	(226)	(226)		
EP080605-O	9.41 x 8.68 x 5.86	7.97 x 5.97 x 5.07	10.04 x 3.64	4.56	6.25	4.25	10.89	8.89	3.2	BP★0806*
EP080605-T	(239 x 223 x 149)	(202 x 152 x 129)	(255 x 92)	(116)	(159)	(108)	(277)	(226)		
EP080805-O	9.41 x 10.68 x 5.86	7.97 x 7.97 x 5.03	10.04 x 5.63	4.53	6.25	6.25	10.88	10.88	4	BP★0808*
EP080805-T	(239 x 271 x 149)	(202 x 202 x 128)	(255 x 143)	(115)	(159)	(159)	(276)	(276)		
EP100806-O	11.41 x 10.68 x 6.36	9.95 x 7.96 x 5.57	12.04 x 5.64	5.05	8.25	6.25	12.89	10.89	4.3	BP★1008*
EP100806-T	(290 x 271 x 161)	(253 x 202 x 142)	(306 x 143)	(128)	(210)	(159)	(327)	(277)		
EP100807-O	11.41 x 10.68 x 7.89	9.95 x 7.95 x 7.06	12.03 x 5.63	6.54	8.25	6.25	12.88	10.88	5	BP★1008*
EP100807-T	(290 x 271 x 200)	(253 x 202 x 179)	(306 x 143)	(166)	(210)	(159)	(327)	(276)		
EP101006-O	11.41 x 12.68 x 6.97	9.95 x 9.95 x 6.15	12.03 x 7.63	5.65	8.25	8.25	12.88	12.88	5	BP★1010*
EP101006-T	(290 x 322 x 177)	(253 x 253 x 156)	(306 x 194)	(144)	(210)	(210)	(327)	(327)		
EP121007-O	13.40 x 12.68 x 7.86	11.95 x 9.95 x 7.07	14.04 x 7.64	6.56	10.25	8.25	14.89	12.89	7	BP★1210*
EP121007-T	(340 x 322 x 200)	(304 x 253 x 180)	(357 x 194)	(167)	(260)	(210)	(378)	(327)		
EP141207-O	15.40 x 14.68 x 7.86	13.95 x 11.95 x 7.07	16.04 x 9.64	6.56	12.25	10.25	16.89	14.89	8	BP★1412*
EP141207-T	(391 x 373 x 200)	(354 x 304 x 180)	(407 x 245)	(167)	(311)	(260)	(429)	(378)		
EP161409-O	17.65 x 16.68 x 9.98	15.93 x 13.93 x 9.20	18.04 x 11.64	8.68	14.25	12.25	18.89	16.89	10	BP★1614*
EP161409-T	(448 x 424 x 253)	(405 x 354 x 234)	(458 x 296)	(220)	(362)	(311)	(480)	(429)		
EP181604-O	19.41 x 18.68 x 5.41	18.16 x 16.16 x 5.08	20.50 x 13.50	4.56	16.25	14.25	21.75	18.68	10	BP★1816*
EP181604-T	(493 x 474 x 137)	(462 x 411 x 129)	(521 x 343)	(116)	(413)	(362)	(552)	(474)		
EP181611-O	19.41 x 18.68 x 11.90	17.83 x 15.83 x 11.08	20.04 x 13.64	10.56	16.25	14.25	20.89	18.89	11.3	BP★1816*
EP181611-T	(493 x 474 x 302)	(453 x 402 x 281)	(509 x 346)	(268)	(413)	(362)	(531)	(480)		
EP201608-O	21.41 x 18.68 x 9.97	19.86 x 15.86 x 9.15	23.15 x 14.75	8.65	18.25	14.25	24.00	20.02	14	BP★2016*
EP201608-T	(544 x 474 x 253)	(504 x 403 x 232)	(588 x 375)	(220)	(464)	(362)	(610)	(509)		
EP242410-O	25.41 x 26.68 x 11.41	23.91 x 23.91 x 11.88	25.69 x 18.00	10.56	22.25	22.25	26.69	21.86	22	BP★2424*
EP242410-T	(645 x 678 x 290)	(607 x 607 x 302)	(653 x 457)	(268)	(565)	(565)	(678)	(555)		

O = opaque, T = tinted

Dimensions are in inches, millimeters in parenthesis. Subject to change without notice.

★ "F" for fiberglass or "A" for aluminum / *Panel sold separately.