

SCREW COVER TYPE 3R ENCLOSURES

Application

Designed to house electrical controls, instruments and components in an outdoor environment. Protects against rain, sleet and snow. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.048" & 0.063" galvanized steel.
- Spot weld construction.
- Rain cap.
- Mounting holes in back of enclosure.
- Slip on removable screw cover.
- Padlocking provisions.
- No gasket.
- No subpanel or provisions.
- Ground studs on door and body.

Options

Optional mounting straps available.

Finish

ANSI-61 gray powder coated inside and out.

IS7 Industry Standards

NEMA Type 3R
UL Listed Type 3R
CSA Type 3R
IEC 60529 IP32



Enclosure Product Code N3

Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard
SCE-4R44	4.00	4.00	4.00	IS7
SCE-6R64	6.00	6.00	4.00	IS7
SCE-6R66	6.00	6.00	6.00	IS7
SCE-8R64	8.00	6.00	4.00	IS7
SCE-8R66	8.00	6.00	6.00	IS7
SCE-10R84	10.00	8.00	4.00	IS7
SCE-10R86	10.00	8.00	6.00	IS7
SCE-10R104	10.00	10.00	4.00	IS7
SCE-10R106	10.00	10.00	6.00	IS7
SCE-12R104	12.00	10.00	4.00	IS7
SCE-12R106	12.00	10.00	6.00	IS7
SCE-12R124	12.00	12.00	4.00	IS7
SCE-12R126	12.00	12.00	6.00	IS7

SCREW COVER TYPE 3R ENCLOSURES TECHNICAL DATA

