

Application

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides a degree of protection from dust, dirt, water and oil. The enclosures are extra deep for applications requiring more interior space.

Construction

- 0.104" stainless steel Type 304.
- Removable and interchangeable doors.
- Stainless steel concealed hinges.
- Seams continuously welded and ground smooth.
- Strong, rigid construction with stiffeners welded on backs of single access boxes.
- Lifting eyes for easy handling.
- Black zinc die cast keylocking/padlocking handle.
- 3-point latching mechanism.
- Latch rods have ramp shoes for easier door closing.
- Flange trough collar around all sides of door opening.
- Removable print pocket provided on door with 3-point latch.
- Mounting channels welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- Pour in place oil and water resistant gasket.
- Ground stud on door and body.
- Provisions for light kit.

Finish

#4 brushed finish on all exterior surfaces. Optional subpanels powder coated white.

Accessories - See page 144-151

IS3 Industry Standards

NEMA Type 3R, 12 & Type 13
UL Listed Type 3R & 12
CSA Type 3R & 12
IEC 60529 IP55

***To maintain Type 3R listing, drainage is required. Install equally rated drainage device or drill a 1/8 to 1/4 inch hole in the bottom center of the enclosure, approximately 1 inch from the right, and 1 inch from the left for drainage, use listed rain-tight or wet location hubs. Drip shield over the door is recommended for all outdoor applications.

Enclosure Product Code S2

Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard
SCE-604818SSFSD	60.00	48.00	18.00	IS3
SCE-724818SSFSD	72.00	48.00	18.00	IS3
SCE-724824SSFSD	72.00	48.00	24.00	IS3
SCE-726018SSFSD	72.00	60.00	18.00	IS3
SCE-726024SSFSD	72.00	60.00	24.00	IS3
SCE-726036SSFSD	72.00	60.00	36.00	IS3
SCE-727218SSFSD	72.00	72.00	18.00	IS3
SCE-727224SSFSD	72.00	72.00	24.00	IS3
SCE-904820SSFSD	90.00	48.00	20.00	IS3
SCE-907220SSFSD	90.00	72.00	20.00	IS3
SCE-907224SSFSD	90.00	72.00	24.00	IS3
SCE-907236SSFSD	90.00	72.00	36.00	IS3

