

POLYCARBONATE PUSHBUTTON ENCLOSURES

Application

Designed for indoor or outdoor use to house electrical and electronic controls, instruments and components in areas that may be regularly hosed down or are in very wet conditions. Non-corrosive, UV resistant polycarbonate enclosure with opaque covers. Provides protection from dust, dirt, oil and water.

Construction

- Impact Resistant Polycarbonate
- Opaque cover.
- Polycarbonate external mounting feet included.
- Oil and water resistant pour in place gasket

Finish

RAL 7035 Light Gray Polycarbonate

IS6 Industry Standards

NEMA Type 3R, 4, 4X, 12 & Type 13
UL Listed Type 3R, 4, 4X & 12
CSA Type 3R, 4, 4X & 12
IEC 60529 IP66



POLYCARBONATE PUSHBUTTON ENCLOSURES TECHNICAL DATA

30.5 MM PUSHBUTTON ENCLOSURE

Enclosure Product Code F1

Catalog No.	Height (A)	Width (B)	Depth (C)	Mounting (G)	Mounting (H)	Internal Standoff	Industry Standard
SCE-1PBPC	4.34	3.16	2.76	3.62	2.44	3.11	IS6
SCE-2PBPC	5.12	3.16	3.51	4.40	2.44	3.11	IS6

22.5 MM PUSHBUTTON ENCLOSURE

Enclosure Product Code F1

Catalog No.	Height (A)	Width (B)	Depth (C)	Mounting (G)	Mounting (H)	Internal Standoff	Industry Standard
SCE-1PBPC1	4.34	3.16	2.76	3.62	2.44	3.11	IS6
SCE-2PBPC1	5.12	3.16	3.51	4.40	2.44	3.11	IS6

