

SLOPE TOP WORK STATION

Application

Designed to house a computer, keyboard, monitor and other additional computer equipment in an industrial environment and provide degree of protection from dust, oil and moisture. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.075" carbon steel.
- Seams continuously welded and ground smooth.
- Pour in place oil and water resistant gasket.
- Flange trough collar around all sides of door opening.
- Concealed hinges.
- Removable doors.
- Ground studs on door and body.
- Large polycarbonate viewing window.
- Lifting eyes for easy handling.
- Black quarter turn latches on top door.
- Black quarter turn wing knob latches on keyboard door.
- Black 3-point flush swing handle in back door.
- Gland plate on lower back of enclosure
- Pullout keyboard shelf with attached self storing mouse shelf and mouse pad.
- Mounting channels welded on sides of interior body for mounting optional subpanels, racks, mounting angles and shelves.

Options

Optional tamper-resistant inserts or padlocking handles are available.

Accessories - See Pages 38-44

Finish

Powder coated white inside and out.

IS1 Industry Standards

NEMA Type 12 & Type 13
UL Listed Type 12
CSA Type 12
IEC 60529 IP55

SLOPE TOP WORK STATION TECHNICAL DATA

Enclosure Product Code C2				
Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard
SCE-66ST2626WS	65.59	26.00	26.00	IS1

