

MOUNTING OPTIONS

FLOOR STAND KIT

Can be installed on most wall-mounted enclosures with a width of 20 inches or more. Can also be installed on SCE free-standing enclosures. Kits include two stands. This configuration can be ordered in special sizes. Consult a factory representative for price and delivery. For specifications, consult our installation manual at www.saginawcontrol.com.

Made of carbon steel and finished with ANSI-61 recoatable gray finish. "LG" parts finished RAL 7035 Gray.

Catalog No.	Height (A)	Width (B)	Finish	Product Code
SCE-FK0418	4.00	18.00	ANSI-61 Gray	P2
SCE-FK0608	6.00	8.00	ANSI-61 Gray	P2
SCE-FK0610	6.00	10.00	ANSI-61 Gray	P2
SCE-FK0612	6.00	12.00	ANSI-61 Gray	P2
SCE-FK0614	6.00	14.00	ANSI-61 Gray	P2
SCE-FK0616	6.00	16.00	ANSI-61 Gray	P2
SCE-FK0618	6.00	18.00	ANSI-61 Gray	P2
SCE-FK0620	6.00	20.00	ANSI-61 Gray	P2
SCE-FK0624	6.00	24.00	ANSI-61 Gray	P2
SCE-FK0636	6.00	36.00	ANSI-61 Gray	P2
SCE-FK1208	12.00	8.00	ANSI-61 Gray	P2
SCE-FK1210	12.00	10.00	ANSI-61 Gray	P2
SCE-FK1212	12.00	12.00	ANSI-61 Gray	P2
SCE-FK1214	12.00	14.00	ANSI-61 Gray	P2
SCE-FK1216	12.00	16.00	ANSI-61 Gray	P2
SCE-FK1218	12.00	18.00	ANSI-61 Gray	P2
SCE-FK1220	12.00	20.00	ANSI-61 Gray	P2
SCE-FK1224	12.00	24.00	ANSI-61 Gray	P2
SCE-FK1512	15.00	12.00	ANSI-61 Gray	P2
SCE-FK1516	15.00	16.00	ANSI-61 Gray	P2
SCE-FK1518	15.00	18.00	ANSI-61 Gray	P2
SCE-FK1524	15.00	24.00	ANSI-61 Gray	P2
SCE-FK1808	18.00	8.00	ANSI-61 Gray	P2
SCE-FK1810	18.00	10.00	ANSI-61 Gray	P2
SCE-FK1812	18.00	12.00	ANSI-61 Gray	P2
SCE-FK1816	18.00	16.00	ANSI-61 Gray	P2
SCE-FK1818	18.00	18.00	ANSI-61 Gray	P2
SCE-FK1824	18.00	24.00	ANSI-61 Gray	P2
SCE-FK2408	24.00	8.00	ANSI-61 Gray	P2
SCE-FK2410	24.00	10.00	ANSI-61 Gray	P2
SCE-FK2412	24.00	12.00	ANSI-61 Gray	P2
SCE-FK2416	24.00	16.00	ANSI-61 Gray	P2
SCE-FK0418LG	4.00	18.00	RAL 7035 Gray	P2
SCE-FK0608LG	6.00	8.00	RAL 7035 Gray	P2
SCE-FK0610LG	6.00	10.00	RAL 7035 Gray	P2
SCE-FK0612LG	6.00	12.00	RAL 7035 Gray	P2
SCE-FK0618LG	6.00	18.00	RAL 7035 Gray	P2
SCE-FK0624LG	6.00	24.00	RAL 7035 Gray	P2
SCE-FK1208LG	12.00	8.00	RAL 7035 Gray	P2
SCE-FK1210LG	12.00	10.00	RAL 7035 Gray	P2
SCE-FK1212LG	12.00	12.00	RAL 7035 Gray	P2
SCE-FK1216LG	12.00	16.00	RAL 7035 Gray	P2
SCE-FK1218LG	12.00	18.00	RAL 7035 Gray	P2
SCE-FK1220LG	12.00	20.00	RAL 7035 Gray	P2
SCE-FK1224LG	12.00	24.00	RAL 7035 Gray	P2
SCE-FK1512LG	15.00	12.00	RAL 7035 Gray	P2
SCE-FK1516LG	15.00	16.00	RAL 7035 Gray	P2
SCE-FK1518LG	15.00	18.00	RAL 7035 Gray	P2
SCE-FK1524LG	15.00	24.00	RAL 7035 Gray	P2
SCE-FK1808LG	18.00	8.00	RAL 7035 Gray	P2
SCE-FK1810LG	18.00	10.00	RAL 7035 Gray	P2
SCE-FK1812LG	18.00	12.00	RAL 7035 Gray	P2
SCE-FK1816LG	18.00	16.00	RAL 7035 Gray	P2
SCE-FK1824LG	18.00	24.00	RAL 7035 Gray	P2
SCE-FK2412LG	24.00	12.00	RAL 7035 Gray	P2
SCE-FK1214-05	12.00	14.00	SCE-05 White	P2
SCE-FK1216-05	12.00	16.00	SCE-05 White	P2

MOUNTING OPTIONS

FLOOR STAND KIT STAINLESS STEEL

Can be installed on most wall-mounted enclosures with a width of 20 inches or more. Can also be installed on SCE free-standing enclosures. Kits include two stands. This configuration can be ordered in special sizes. Consult a factory representative for price and delivery. For specifications, consult our installation manual at www.saginawcontrol.com.

"SS" parts are made of stainless steel Type 304 with #4 brushed finish. "SS6" parts are made of stainless steel Type 316/316L with #4 brushed finish

Catalog No.	Height (A)	Width (B)	Finish	Product Code
SCE-FK0616SS	6.00	16.00	#4 Brushed Finish	P2
SCE-FK0618SS	6.00	18.00	#4 Brushed Finish	P2
SCE-FK0624SS	6.00	24.00	#4 Brushed Finish	P2
SCE-FK1208SS	12.00	8.00	#4 Brushed Finish	P2
SCE-FK1210SS	12.00	10.00	#4 Brushed Finish	P2
SCE-FK1212SS	12.00	12.00	#4 Brushed Finish	P2
SCE-FK1216SS	12.00	16.00	#4 Brushed Finish	P2
SCE-FK1218SS	12.00	18.00	#4 Brushed Finish	P2
SCE-FK1220SS	12.00	20.00	#4 Brushed Finish	P2
SCE-FK1224SS	12.00	24.00	#4 Brushed Finish	P2
SCE-FK1512SS	15.00	12.00	#4 Brushed Finish	P2
SCE-FK1518SS	15.00	18.00	#4 Brushed Finish	P2
SCE-FK1524SS	15.00	24.00	#4 Brushed Finish	P2
SCE-FK1812SS	18.00	12.00	#4 Brushed Finish	P2
SCE-FK1818SS	18.00	18.00	#4 Brushed Finish	P2
SCE-FK2410SS	24.00	10.00	#4 Brushed Finish	P2
SCE-FK2412SS	24.00	12.00	#4 Brushed Finish	P2
SCE-FK2416SS	24.00	16.00	#4 Brushed Finish	P2
SCE-FK1212SS6	12.00	12.00	#4 Brushed Finish	P2
SCE-FK1216SS6	12.00	16.00	#4 Brushed Finish	P2
SCE-FK1218SS6	12.00	18.00	#4 Brushed Finish	P2
SCE-FK1224SS6	12.00	24.00	#4 Brushed Finish	P2
SCE-FK1512SS6	15.00	12.00	#4 Brushed Finish	P2
SCE-FK1518SS6	15.00	18.00	#4 Brushed Finish	P2
SCE-FK1524SS6	15.00	24.00	#4 Brushed Finish	P2
SCE-FK1818SS6	18.00	18.00	#4 Brushed Finish	P2
SCE-FK2412SS6	24.00	12.00	#4 Brushed Finish	P2

