

Application

Designed to house electrical controls, instruments and components in areas, which may be regularly hosed down or are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.063" carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Pour in place oil and water resistant gasket.
- Standoffs provided for mounting optional subpanels.
- Removable hinge.
- Doors open 180 degrees.
- Black mini quarter turn latches.
- Latches are opened or closed with a screwdriver.
- Sealing washers and hole plugs included.
- Ground stud on door & body.
- Mounting feet included.

Finish

RAL 7035 gray powder coated inside and out. Optional subpanels powder coated white.

IS4 Industry Standards

NEMA Type 3R, 4, 12 & Type 13
UL Listed Type 3R, 4 & 12
CSA Type 3R, 4 & 12
IEC 60529 IP66

***To maintain Type 3R listing, drainage is required. Install equally rated drainage device or drill a 1/8 to 1/4 inch hole in the bottom center of the enclosure, approximately 1 inch from the right, and 1 inch from the left for drainage, use listed rain-tight or wet location hubs. Drip shield over the door is recommended for all outdoor applications.



Enclosure Product Code E1					Subpanel (P3)		
Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-604ELJLG	6.00	4.00	4.00	IS4	SCE-6P4	5.00	3.00
SCE-606ELJLG	6.00	6.00	4.00	IS4	SCE-6P6	5.00	5.00
SCE-806ELJLG	8.00	6.00	4.00	IS4	SCE-8P6	7.00	5.00
SCE-8066ELJLG	8.00	6.00	6.00	IS4	SCE-8P6	7.00	5.00
SCE-808ELJLG	8.00	8.00	4.00	IS4	SCE-8P8	7.00	7.00
SCE-8086ELJLG	8.00	8.00	6.00	IS4	SCE-8P8	7.00	7.00
SCE-1008ELJLG	10.00	8.00	4.00	IS4	SCE-10P8	9.00	7.00
SCE-10086ELJLG	10.00	8.00	6.00	IS4	SCE-10P8	9.00	7.00
SCE-10106ELJLG	10.00	10.00	6.00	IS4	SCE-10P10	9.00	9.00
SCE-1210ELJLG	12.00	10.00	6.00	IS4	SCE-12P10	11.00	9.00
SCE-12108ELJLG	12.00	10.00	8.00	IS4	SCE-12P10	11.00	9.00
SCE-1212ELJLG	12.00	12.00	6.00	IS4	SCE-12P12	11.00	11.00
SCE-1412ELJLG	14.00	12.00	6.00	IS4	SCE-14P12	13.00	11.00
SCE-14128ELJLG	14.00	12.00	8.00	IS4	SCE-14P12	13.00	11.00
SCE-1614ELJLG	16.00	14.00	6.00	IS4	SCE-16P14	15.00	13.00
SCE-16148ELJLG	16.00	14.00	8.00	IS4	SCE-16P14	15.00	13.00
SCE-20166ELJLG	20.00	16.00	6.00	IS4	SCE-20P16J/GALV	19.00	15.00
SCE-20168ELJLG	20.00	16.00	8.00	IS4	SCE-20P16J/GALV	19.00	15.00
SCE-201610ELJLG	20.00	16.00	10.00	IS4	SCE-20P16J/GALV	19.00	15.00
SCE-20206ELJLG	20.00	20.00	6.00	IS4	SCE-20P20J/GALV	19.00	19.00
SCE-20208ELJLG	20.00	20.00	8.00	IS4	SCE-20P20J/GALV	19.00	19.00
SCE-202010ELJLG	20.00	20.00	10.00	IS4	SCE-20P20J/GALV	19.00	19.00

