

ENVIROLINE® SERIES SINGLE-DOOR ENCLOSURES

Application

Designed to house electrical and electronic controls, instruments and components. Provides protection from dust, oil and water. For outdoor applications a drip shield is recommended. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.075" carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Pour in place oil and water resistant gasket.
- Collar studs provided for mounting optional subpanels.
- Concealed hinges.
- Removable and interchangeable doors.
- Black quarter turn latches.
- Latches are opened or closed with a screwdriver.
- Mounting holes in back of enclosure.
- Mounting hardware, sealing washers and hole plugs included.
- Removable print pocket furnished if height and width of enclosure is greater than 12".
- Ground studs on door and body.
- Provision for Lifting Lugs included on enclosures with Height >48" and with Depth >16". Lifting Lug assembly included with the enclosure bolt pack.

Finish

ANSI-61 gray powder coated inside and out.
Optional subpanels powder coated white.

Options

- Optional tamper-resistant inserts available.
- Optional mounting feet available.
- Door hardware available.

Notes

Interchangeable latches and handles available in the accessory section.

IS4 Industry Standards

NEMA Type 3R, 4, 12 & Type 13
UL Listed Type 3R, 4 & 12
CSA Type 3R, 4 & 12
IEC 60529 IP66

***To maintain Type 3R listing, drainage is required. Install equally rated drainage device or drill a 1/8 to 1/4 inch hole in the bottom center of the enclosure, approximately 1 inch from the right, and 1 inch from the left for drainage, use listed rain-tight or wet location hubs. Drip shield over the door is recommended for all outdoor applications.

Enclosure Product Code E3

Subpanel (P3)

Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-12EL1206LP	12.00	12.00	6.00	IS4	SCE-12DLP12	9.00	9.00
SCE-12EL2406LP	12.00	24.00	6.00	IS4	SCE-12P24	9.00	21.00
SCE-12EL2408LP	12.00	24.00	8.00	IS4	SCE-12P24	9.00	21.00
SCE-16EL1206LP	16.00	12.00	6.00	IS4	SCE-16P12	13.00	9.00
SCE-16EL1208LP	16.00	12.00	8.00	IS4	SCE-16P12	13.00	9.00
SCE-16EL1408LP	16.00	14.00	8.00	IS4	SCE-16DLP14	13.00	11.00
SCE-16EL1606LP	16.00	16.00	6.00	IS4	SCE-16P16	13.00	13.00
SCE-16EL1608LP	16.00	16.00	8.00	IS4	SCE-16P16	13.00	13.00
SCE-16EL2006LP	16.00	20.00	6.00	IS4	SCE-20P16	17.00	13.00
SCE-16EL2008LP	16.00	20.00	8.00	IS4	SCE-20P16	17.00	13.00
SCE-20EL1206LP	20.00	12.00	6.00	IS4	SCE-20P12	17.00	9.00
SCE-20EL1606LP	20.00	16.00	6.00	IS4	SCE-20P16	17.00	13.00
SCE-20EL1608LP	20.00	16.00	8.00	IS4	SCE-20P16	17.00	13.00
SCE-20EL1612LP	20.00	16.00	12.00	IS4	SCE-20P16	17.00	13.00
SCE-20EL2006LP	20.00	20.00	6.00	IS4	SCE-20P20	17.00	17.00
SCE-20EL2008LP	20.00	20.00	8.00	IS4	SCE-20P20	17.00	17.00
SCE-20EL2010LP	20.00	20.00	10.00	IS4	SCE-20P20	17.00	17.00
SCE-20EL2012LP	20.00	20.00	12.00	IS4	SCE-20P20	17.00	17.00
SCE-20EL2408LP	20.00	24.00	8.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL1206LP	24.00	12.00	6.00	IS4	SCE-12P24	9.00	21.00
SCE-24EL1606LP	24.00	16.00	6.00	IS4	SCE-24P16	21.00	13.00
SCE-24EL1608LP	24.00	16.00	8.00	IS4	SCE-24P16	21.00	13.00
SCE-24EL2006LP	24.00	20.00	6.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2008LP	24.00	20.00	8.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2010LP	24.00	20.00	10.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2012LP	24.00	20.00	12.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2016LP	24.00	20.00	16.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2406LP	24.00	24.00	6.00	IS4	SCE-24P24	21.00	21.00
SCE-24EL2408LP	24.00	24.00	8.00	IS4	SCE-24P24	21.00	21.00
SCE-24EL2410LP	24.00	24.00	10.00	IS4	SCE-24P24	21.00	21.00
SCE-24EL2412LP	24.00	24.00	12.00	IS4	SCE-24P24	21.00	21.00
SCE-24EL2416LP	24.00	24.00	16.00	IS4	SCE-24P24	21.00	21.00
SCE-24EL3008LP	24.00	30.00	8.00	IS4	SCE-30P24	27.00	21.00
SCE-24EL3010LP	24.00	30.00	10.00	IS4	SCE-30P24	27.00	21.00
SCE-24EL3012LP	24.00	30.00	12.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL1606LP	30.00	16.00	6.00	IS4	SCE-30P16	27.00	13.00
SCE-30EL2008LP	30.00	20.00	8.00	IS4	SCE-30P20	27.00	17.00
SCE-30EL2010LP	30.00	20.00	10.00	IS4	SCE-30P20	27.00	17.00
SCE-30EL2406LP	30.00	24.00	6.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2408LP	30.00	24.00	8.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2410LP	30.00	24.00	10.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2412LP	30.00	24.00	12.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2416LP	30.00	24.00	16.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2420LP	30.00	24.00	20.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2424LP	30.00	24.00	24.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL3008LP	30.00	30.00	8.00	IS4	SCE-30P30	27.00	27.00
SCE-30EL3010LP	30.00	30.00	10.00	IS4	SCE-30P30	27.00	27.00
SCE-30EL3012LP	30.00	30.00	12.00	IS4	SCE-30P30	27.00	27.00
SCE-30EL3608LP	30.00	36.00	8.00	IS4	SCE-36P30	33.00	27.00
SCE-30EL3610LP	30.00	36.00	10.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL2408LP	36.00	24.00	8.00	IS4	SCE-36P24	33.00	21.00

ENVIROLINE® SERIES SINGLE-DOOR ENCLOSURES

Enclosure Product Code E3

Subpanel (P3)

Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-36EL2410LP	36.00	24.00	10.00	IS4	SCE-36P24	33.00	21.00
SCE-36EL2412LP	36.00	24.00	12.00	IS4	SCE-36P24	33.00	21.00
SCE-36EL2416LP	36.00	24.00	16.00	IS4	SCE-36P24	33.00	21.00
SCE-36EL3008LP	36.00	30.00	8.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3010LP	36.00	30.00	10.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3012LP	36.00	30.00	12.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3016LP	36.00	30.00	16.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3020LP	36.00	30.00	20.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3608LP	36.00	36.00	8.00	IS4	SCE-36P36	33.00	33.00
SCE-36EL3610LP	36.00	36.00	10.00	IS4	SCE-36P36	33.00	33.00
SCE-36EL3612LP	36.00	36.00	12.00	IS4	SCE-36P36	33.00	33.00
SCE-36EL3616LP	36.00	36.00	16.00	IS4	SCE-36P36	33.00	33.00
SCE-40EL2412LP	40.00	24.00	12.00	IS4	SCE-40P24	37.00	21.00
SCE-42EL2410LP	42.00	24.00	10.00	IS4	SCE-42P24	39.00	21.00
SCE-42EL3008LP	42.00	30.00	8.00	IS4	SCE-42P30	39.00	27.00
SCE-42EL3010LP	42.00	30.00	10.00	IS4	SCE-42P30	39.00	27.00
SCE-42EL3012LP	42.00	30.00	12.00	IS4	SCE-42P30	39.00	27.00
SCE-42EL3016LP	42.00	30.00	16.00	IS4	SCE-42P30	39.00	27.00
SCE-42EL3608LP	42.00	36.00	8.00	IS4	SCE-42P36	39.00	33.00
SCE-42EL3610LP	42.00	36.00	10.00	IS4	SCE-42P36	39.00	33.00
SCE-42EL3612LP	42.00	36.00	12.00	IS4	SCE-42P36	39.00	33.00
SCE-42EL3616LP	42.00	36.00	16.00	IS4	SCE-42P36	39.00	33.00
SCE-48EL2408LP	48.00	24.00	8.00	IS4	SCE-48P24	45.00	21.00
SCE-48EL2412LP	48.00	24.00	12.00	IS4	SCE-48P24	45.00	21.00
SCE-48EL3008LP	48.00	30.00	8.00	IS4	SCE-48P30	45.00	27.00
SCE-48EL3010LP	48.00	30.00	10.00	IS4	SCE-48P30	45.00	27.00
SCE-48EL3012LP	48.00	30.00	12.00	IS4	SCE-48P30	45.00	27.00
SCE-48EL3016LP	48.00	30.00	16.00	IS4	SCE-48P30	45.00	27.00
SCE-48EL3608LP	48.00	36.00	8.00	IS4	SCE-48P36	45.00	33.00
SCE-48EL3610LP	48.00	36.00	10.00	IS4	SCE-48P36	45.00	33.00
SCE-48EL3612LP	48.00	36.00	12.00	IS4	SCE-48P36	45.00	33.00
SCE-48EL3616LP	48.00	36.00	16.00	IS4	SCE-48P36	45.00	33.00
SCE-48EL3620LP	48.00	36.00	20.00	IS4	SCE-48P36	45.00	33.00
SCE-60EL2412LP	60.00	24.00	12.00	IS4	SCE-60P24	57.00	21.00
SCE-60EL3608LP	60.00	36.00	8.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3610LP	60.00	36.00	10.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3612LP	60.00	36.00	12.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3616LP	60.00	36.00	16.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3620LP	60.00	36.00	20.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3624LP	60.00	36.00	24.00	IS4	SCE-60P36	57.00	33.00
SCE-72EL3012LP	72.00	30.00	12.00	IS4	SCE-72P30	69.00	27.00
SCE-72EL3016LP	72.00	30.00	16.00	IS4	SCE-72P30	69.00	27.00
SCE-72EL3024LP	72.00	30.00	24.00	IS4	SCE-72P30	69.00	27.00
SCE-72EL3612LP	72.00	36.00	12.00	IS4	SCE-72P36	69.00	33.00
SCE-72EL3616LP	72.00	36.00	16.00	IS4	SCE-72P36	69.00	33.00
SCE-72EL3624LP	72.00	36.00	24.00	IS4	SCE-72P36	69.00	33.00

