

Application

Designed to house electrical and electronic controls, instrumentation and components in indoor or outdoor locations. For outdoor applications a drip shield is recommended. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.075" carbon steel.
- Seams continuously welded and ground smooth.
- Flange trough collar around all sides of door opening.
- Collar studs provided for mounting optional subpanels.
- Mounting holes in back of the enclosure for wall-mounting.
- Mounting hardware, sealing washers and hole plugs included.
- Concealed hinges.
- Removable and interchangeable doors.
- Black zinc die cast keylocking/padlocking handles.
- 3-point latching mechanism.
- Black quarter turn latches as required.
- Removable print pocket.
- Oil and water resistant gasket.
- Ground stud on door and body.
- Provision for Lifting Lugs included on enclosures with Height >48" and with Depth >16". Lifting Lug assembly included with the enclosure bolt pack.

Finish

ANSI-61 gray powder coated inside and out. Optional subpanels powder coated white.

IS4 Industry Standards

NEMA Type 3R, 4, 12 & Type 13
UL Listed Type 3R, 4 & 12
CSA Type 3R, 4 & 12
IEC 60529 IP66

***To maintain Type 3R listing, drainage is required. Install equally rated drainage device or drill a 1/8 to 1/4 inch hole in the bottom center of the enclosure, approximately 1 inch from the right, and 1 inch from the left for drainage, use listed rain-tight or wet location hubs. Drip shield over the door is recommended for all outdoor applications.

Catalog No.	Enclosure Product Code E3				Subpanel (P3)		
	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-24EL2010LPPL	24.00	20.00	10.00	IS4	SCE-24P20	21.00	17.00
SCE-24EL2410LPPL	24.00	24.00	10.00	IS4	SCE-24P24	21.00	21.00
SCE-30EL2412LPPL	24.00	24.00	12.00	IS4	SCE-24P24	21.00	21.00
SCE-30EL2410LPPL	30.00	24.00	10.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2412LPPL	30.00	24.00	12.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL2416LPPL	30.00	24.00	16.00	IS4	SCE-30P24	27.00	21.00
SCE-30EL3012LPPL	30.00	30.00	12.00	IS4	SCE-30P30	27.00	27.00
SCE-36EL2412LPPL	36.00	24.00	12.00	IS4	SCE-36P24	33.00	21.00
SCE-36EL3012LPPL	36.00	30.00	12.00	IS4	SCE-36P30	33.00	27.00
SCE-36EL3612LPPL	36.00	36.00	12.00	IS4	SCE-36P36	33.00	33.00
SCE-42EL3612LPPL	42.00	36.00	12.00	IS4	SCE-42P36	39.00	33.00
SCE-48EL3612LPPL	48.00	36.00	12.00	IS4	SCE-48P36	45.00	33.00
SCE-48EL3616LPPL	48.00	36.00	16.00	IS4	SCE-48P36	45.00	33.00
SCE-60EL3612LPPL	60.00	36.00	12.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3616LPPL	60.00	36.00	16.00	IS4	SCE-60P36	57.00	33.00
SCE-60EL3624LPPL	60.00	36.00	24.00	IS4	SCE-60P36	57.00	33.00
SCE-72EL3624LPPL	72.00	36.00	24.00	IS4	SCE-72P36	69.00	33.00

