

CLAMP FASTENED SINGLE-DOOR ENCLOSURES

Application

Designed to house electrical and electronic controls, instruments, and components. Provides protection from dust, dirt, oil and water. For installation information, consult our installation manual at www.saginawcontrol.com.

Construction

- 0.075" carbon steel.
- Seams continuously welded and ground smooth, no holes or knockouts.
- Flange trough collar around all sides of door opening.
- Door clamps are quick and easy to operate.
- Concealed hinges.
- Hasp and staple for padlocking.
- Pour in place oil and water resistant gasket.
- Collar studs for mounting optional subpanels.
- Ground stud on door and body.
- Removable print pocket furnished if height and width of enclosure is greater than 12".
- Bolt-on mounting provisions top and bottom of back.
- Provision for Lifting Lugs included on enclosures with Height >48" and with Depth >16". Lifting Lug assembly included with the enclosure bolt pack.

Finish

ANSI-61 gray powder coated inside and out. Optional subpanels powder coated white.

IS4 Industry Standards

NEMA Type 3R, 4, 12 & Type 13
UL Listed Type 3R, 4 & 12
CSA Type 3R, 4 & 12
IEC 60529 IP66

***To maintain Type 3R listing, drainage is required. Install equally rated drainage device or drill a 1/8 to 1/4 inch hole in the bottom center of the enclosure, approximately 1 inch from the right, and 1 inch from the left for drainage, use listed rain-tight or wet location hubs. Drip shield over the door is recommended for all outdoor applications.

CLAMP FASTENED SINGLE-DOOR ENCLOSURES

Enclosure Product Code E3					Subpanel (P3)		
Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-12H2406LP	12.00	24.00	6.00	IS4	SCE-12P24	9.00	21.00
SCE-12H2408LP	12.00	24.00	8.00	IS4	SCE-12P24	9.00	21.00
SCE-16H1206LP	16.00	12.00	6.00	IS4	SCE-16P12	13.00	9.00
SCE-16H1208LP	16.00	12.00	8.00	IS4	SCE-16P12	13.00	9.00
SCE-16H1210LP	16.00	12.00	10.00	IS4	SCE-16P12	13.00	9.00
SCE-16H1606LP	16.00	16.00	6.00	IS4	SCE-16P16	13.00	13.00
SCE-16H1608LP	16.00	16.00	8.00	IS4	SCE-16P16	13.00	13.00
SCE-16H2006LP	16.00	20.00	6.00	IS4	SCE-20P16	17.00	13.00
SCE-16H2008LP	16.00	20.00	8.00	IS4	SCE-20P16	17.00	13.00
SCE-20H1206LP	20.00	12.00	6.00	IS4	SCE-20P12	17.00	9.00
SCE-20H1208LP	20.00	12.00	8.00	IS4	SCE-20P12	17.00	9.00
SCE-20H1606LP	20.00	16.00	6.00	IS4	SCE-20P16	17.00	13.00
SCE-20H1608LP	20.00	16.00	8.00	IS4	SCE-20P16	17.00	13.00
SCE-20H1610LP	20.00	16.00	10.00	IS4	SCE-20P16	17.00	13.00
SCE-20H1612LP	20.00	16.00	12.00	IS4	SCE-20P16	17.00	13.00
SCE-20H2006LP	20.00	20.00	6.00	IS4	SCE-20P20	17.00	17.00
SCE-20H2008LP	20.00	20.00	8.00	IS4	SCE-20P20	17.00	17.00
SCE-20H2010LP	20.00	20.00	10.00	IS4	SCE-20P20	17.00	17.00
SCE-20H2406LP	20.00	24.00	6.00	IS4	SCE-24P20	21.00	17.00
SCE-20H2408LP	20.00	24.00	8.00	IS4	SCE-24P20	21.00	17.00
SCE-20H3006LP	20.00	30.00	6.00	IS4	SCE-30P20	27.00	17.00
SCE-24H1206LP	24.00	12.00	6.00	IS4	SCE-12P24	9.00	21.00
SCE-24H1208LP	24.00	12.00	8.00	IS4	SCE-12P24	9.00	21.00
SCE-24H1210LP	24.00	12.00	10.00	IS4	SCE-12P24	9.00	21.00
SCE-24H1606LP	24.00	16.00	6.00	IS4	SCE-24P16	21.00	13.00
SCE-24H1608LP	24.00	16.00	8.00	IS4	SCE-24P16	21.00	13.00
SCE-24H2006LP	24.00	20.00	6.00	IS4	SCE-24P20	21.00	17.00
SCE-24H2008LP	24.00	20.00	8.00	IS4	SCE-24P20	21.00	17.00
SCE-24H2010LP	24.00	20.00	10.00	IS4	SCE-24P20	21.00	17.00
SCE-24H2012LP	24.00	20.00	12.00	IS4	SCE-24P20	21.00	17.00
SCE-24H2016LP	24.00	20.00	16.00	IS4	SCE-24P20	21.00	17.00
SCE-24H2406LP	24.00	24.00	6.00	IS4	SCE-24P24	21.00	21.00
SCE-24H2408LP	24.00	24.00	8.00	IS4	SCE-24P24	21.00	21.00
SCE-24H2410LP	24.00	24.00	10.00	IS4	SCE-24P24	21.00	21.00
SCE-24H2412LP	24.00	24.00	12.00	IS4	SCE-24P24	21.00	21.00
SCE-24H2416LP	24.00	24.00	16.00	IS4	SCE-24P24	21.00	21.00
SCE-24H3008LP	24.00	30.00	8.00	IS4	SCE-30P24	27.00	21.00
SCE-30H1606LP	30.00	16.00	6.00	IS4	SCE-30P16	27.00	13.00
SCE-30H2006LP	30.00	20.00	6.00	IS4	SCE-30P20	27.00	17.00
SCE-30H2008LP	30.00	20.00	8.00	IS4	SCE-30P20	27.00	17.00
SCE-30H2010LP	30.00	20.00	10.00	IS4	SCE-30P20	27.00	17.00
SCE-30H2406LP	30.00	24.00	6.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2408LP	30.00	24.00	8.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2410LP	30.00	24.00	10.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2412LP	30.00	24.00	12.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2416LP	30.00	24.00	16.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2420LP	30.00	24.00	20.00	IS4	SCE-30P24	27.00	21.00
SCE-30H2424LP	30.00	24.00	24.00	IS4	SCE-30P24	27.00	21.00
SCE-30H3008LP	30.00	30.00	8.00	IS4	SCE-30P30	27.00	27.00
SCE-30H3012LP	30.00	30.00	12.00	IS4	SCE-30P30	27.00	27.00
SCE-30H3608LP	30.00	36.00	8.00	IS4	SCE-36P30	33.00	27.00
SCE-36H1606LP	36.00	16.00	6.00	IS4	SCE-36P16	33.00	13.00
SCE-36H2406LP	36.00	24.00	6.00	IS4	SCE-36P24	33.00	21.00

Enclosure Product Code E3					Subpanel (P3)		
Catalog No.	Height (A)	Width (B)	Depth (C)	Industry Standard	Catalog No.	Panel Height (D)	Panel Width (E)
SCE-36H2408LP	36.00	24.00	8.00	IS4	SCE-36P24	33.00	21.00
SCE-36H2410LP	36.00	24.00	10.00	IS4	SCE-36P24	33.00	21.00
SCE-36H2412LP	36.00	24.00	12.00	IS4	SCE-36P24	33.00	21.00
SCE-36H2416LP	36.00	24.00	16.00	IS4	SCE-36P24	33.00	21.00
SCE-36H3006LP	36.00	30.00	6.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3008LP	36.00	30.00	8.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3010LP	36.00	30.00	10.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3012LP	36.00	30.00	12.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3016LP	36.00	30.00	16.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3020LP	36.00	30.00	20.00	IS4	SCE-36P30	33.00	27.00
SCE-36H3608LP	36.00	36.00	8.00	IS4	SCE-36P36	33.00	33.00
SCE-36H3612LP	36.00	36.00	12.00	IS4	SCE-36P36	33.00	33.00
SCE-36H3616LP	36.00	36.00	16.00	IS4	SCE-36P36	33.00	33.00
SCE-42H2408LP	42.00	24.00	8.00	IS4	SCE-42P24	39.00	21.00
SCE-42H3008LP	42.00	30.00	8.00	IS4	SCE-42P30	39.00	27.00
SCE-42H3010LP	42.00	30.00	10.00	IS4	SCE-42P30	39.00	27.00
SCE-42H3012LP	42.00	30.00	12.00	IS4	SCE-42P30	39.00	27.00
SCE-42H3016LP	42.00	30.00	16.00	IS4	SCE-42P30	39.00	27.00
SCE-42H3608LP	42.00	36.00	8.00	IS4	SCE-42P36	39.00	33.00
SCE-42H3610LP	42.00	36.00	10.00	IS4	SCE-42P36	39.00	33.00
SCE-42H3612LP	42.00	36.00	12.00	IS4	SCE-42P36	39.00	33.00
SCE-42H3616LP	42.00	36.00	16.00	IS4	SCE-42P36	39.00	33.00
SCE-48H2408LP	48.00	24.00	8.00	IS4	SCE-48P24	45.00	21.00
SCE-48H3008LP	48.00	30.00	8.00	IS4	SCE-48P30	45.00	27.00
SCE-48H3010LP	48.00	30.00	10.00	IS4	SCE-48P30	45.00	27.00
SCE-48H3016LP	48.00	30.00	16.00	IS4	SCE-48P30	45.00	27.00
SCE-48H3608LP	48.00	36.00	8.00	IS4	SCE-48P36	45.00	33.00
SCE-48H3610LP	48.00	36.00	10.00	IS4	SCE-48P36	45.00	33.00
SCE-48H3612LP	48.00	36.00	12.00	IS4	SCE-48P36	45.00	33.00
SCE-48H3616LP	48.00	36.00	16.00	IS4	SCE-48P36	45.00	33.00
SCE-48H3620LP	48.00	36.00	20.00	IS4	SCE-48P36	45.00	33.00
SCE-60H3608LP	60.00	36.00	8.00	IS4	SCE-60P36	57.00	33.00
SCE-60H3610LP	60.00	36.00	10.00	IS4	SCE-60P36	57.00	33.00
SCE-60H3612LP	60.00	36.00	12.00	IS4	SCE-60P36	57.00	33.00
SCE-60H3616LP	60.00	36.00	16.00	IS4	SCE-60P36	57.00	33.00
SCE-60H3620LP	60.00	36.00	20.00	IS4	SCE-60P36	57.00	33.00
SCE-72H3012LP	72.00	30.00	12.00	IS4	SCE-72P30	69.00	27.00
SCE-72H3016LP	72.00	30.00	16.00	IS4	SCE-72P30	69.00	27.00
SCE-72H3024LP	72.00	30.00	24.00	IS4	SCE-72P30	69.00	27.00
SCE-72H3612LP	72.00	36.00	12.00	IS4	SCE-72P36	69.00	33.00
SCE-72H3616LP	72.00	36.00	16.00	IS4	SCE-72P36	69.00	33.00

