



Your Enclosure Source®

Saginaw Control and Engineering  
95 Midland Road Saginaw, MI 48638-5770  
(800) 234-6871 - Fax: (989) 799-4524  
SCE@SaginawControl.com

## SCE-12N1204NKLP

### Product Specifications:

**Part Number:** SCE-12N1204NKLP  
**Description:** Nema-1 Enclosure w/Knockouts  
**Height:** 12.00"  
**Width:** 12.00"  
**Depth:** 4.00"  
**Price Code:** N1  
**List Price:** \$73.42  
**Catalog Page:** 999  
**Est. Ship Weight:** 10.00 lbs



#### Construction

- \* 0.048 In., 0.063 In. & 0.075 In. carbon steel depending on enclosure size.
- \* Spot weld construction.
- \* Knockouts provided in the top, bottom right and left side.
- \* Standoffs provided for mounting optional panels.
- \* Doors open 180 degrees.
- \* Black quarter turn latches
- \* Latches are opened and closed with a screwdriver.
- \* Ground stud on door.
- \* Mounting holes in back of enclosure
- \* Butt Hinge - Black

#### Application

Designed to house electrical controls, instruments and components in areas that do not require oil, water and dust tight protection.

#### Finish

ANSI-61 gray powder coating inside and out. Optional sub-panels are powder coated white.

#### Industry Standards - (IS8)

- \* NEMA Type 1
- \* UL Listed Type 1
- \* CSA Type 1
- \* IEC 60529
- \* IP 30

#### Optional Accessories

SCE-12N12MP Subpanel, Flat Nema-1  
SCE-12N12MPP Subpanel, Flat Perforated  
SCE-DLKLDB Keylocking Door Latch (Black)  
SCE-DLSBPA Quarter Turn, Nema 1  
SCE-NMST12 Strap, Nema-1 Mounting

#### Similar Part Numbers

SCE-10N1004NKLP Nema-1 Enclosure w/Knockouts  
SCE-10N1006NKLP Nema-1 Enclosure w/Knockouts  
SCE-10N804NKLP Nema-1 Enclosure w/Knockouts  
SCE-10N806NKLP Nema-1 Enclosure w/Knockouts  
SCE-12N1004NKLP Nema-1 Enclosure w/Knockouts  
SCE-12N1006NKLP Nema-1 Enclosure w/Knockouts  
SCE-12N1206NKLP Nema-1 Enclosure w/Knockouts  
SCE-12N1208NKLP Nema-1 Enclosure w/Knockouts  
SCE-14N1204NKLP Nema-1 Enclosure w/Knockouts  
SCE-14N1206NKLP Nema-1 Enclosure w/Knockouts