



Your Enclosure Source®

Saginaw Control and Engineering
95 Midland Road Saginaw, MI 48638-5770
(800) 234-6871 - Fax: (989) 799-4524
SCE@SaginawControl.com

SCE-12N1206NKLP

Product Specifications:

Part Number: SCE-12N1206NKLP

Description: Nema-1 Enclosure w/Knockouts

Height: 12.00"

Width: 12.00"

Depth: 6.00"

Price Code: N1

List Price: \$83.23

Catalog Page: 999

Est. Ship Weight: 9.00 lbs



Construction

- * 0.048 In., 0.063 In. & 0.075 In. carbon steel depending on enclosure size.
- * Spot weld construction.
- * Knockouts provided in the top, bottom right and left side.
- * Standoffs provided for mounting optional panels.
- * Doors open 180 degrees.
- * Black quarter turn latches
- * Latches are opened and closed with a screwdriver.
- * Ground stud on door.
- * Mounting holes in back of enclosure
- * Butt Hinge - Black

Application

Designed to house electrical controls, instruments and components in areas that do not require oil, water and dust tight protection.

Finish

ANSI-61 gray powder coating inside and out. Optional sub-panels are powder coated white.

Industry Standards - (IS8)

- * NEMA Type 1
- * UL Listed Type 1
- * CSA Type 1
- * IEC 60529
- * IP 30

Optional Accessories

- SCE-12N12MP Subpanel, Flat Nema-1
- SCE-12N12MPP Subpanel, Flat Perforated
- SCE-DLKLDB Keylocking Door Latch (Black)
- SCE-DLSBPA Quarter Turn, Nema 1
- SCE-NMST12 Strap, Nema-1 Mounting

Similar Part Numbers

- SCE-10N1004NKLP Nema-1 Enclosure w/Knockouts
- SCE-10N1006NKLP Nema-1 Enclosure w/Knockouts
- SCE-10N804NKLP Nema-1 Enclosure w/Knockouts
- SCE-10N806NKLP Nema-1 Enclosure w/Knockouts
- SCE-12N1004NKLP Nema-1 Enclosure w/Knockouts
- SCE-12N1006NKLP Nema-1 Enclosure w/Knockouts
- SCE-12N1204NKLP Nema-1 Enclosure w/Knockouts
- SCE-12N1208NKLP Nema-1 Enclosure w/Knockouts
- SCE-14N1204NKLP Nema-1 Enclosure w/Knockouts
- SCE-14N1206NKLP Nema-1 Enclosure w/Knockouts