

Technical drawings of a flush mount frame, showing side and end views with dimensions and callouts.

Left Side Detail:

- Overall height: 19.85
- Top section height: 1.00 typ.
- Section height: 8.93 typ.
- Section height: 4.68 typ.
- Section height: .55 typ.
- Reference height: 10.50 REF.
- Notched for concealed hinge clearance (typ.)
- Bottom section height: .88 typ.
- Bottom section height: .30 typ.
- Bottom section height: .281 (x3)
- Bottom section height: .218 (x2)

Right Side Detail:

- Overall height: 19.85
- Top section height: .55 typ.
- Section height: 4.68 typ.
- Reference height: 10.50 REF.
- Section height: 8.93 typ.
- Section height: 1.00 typ.
- Bottom section height: .88 typ.
- Bottom section height: .30 typ.
- Bottom section height: .218 (x2)
- Bottom section height: .281 (x3)

Flush Mount Frame Left Side Detail:

- Top section width: 1.25
- Section width: 1.00
- Section width: 1.25

Flush Mount Frame Right Side Detail:

- Top section width: 1.25
- Section width: 1.00
- Section width: 1.25