

## 8. VBB/VBS

Table-4 2-Way Brass Trim Valve Bodies

Size	Part Number	End Connection	Cv (Kv)
1/2"	VBB2N00	NPT	0.3 (0.3)
	VBB2N01		0.7 (0.6)
	VBB2N02		1.2 (1.0)
	VBB2N03		2.1 (1.8)
	VBB2N04		3.5 (3.0)
	VBB2N05		4.7 (4.1)
	VBB2N06		7.7 (6.7)
	VBB2N07 <sup>b</sup>		10 (8.7)
3/4"	VBB2N10		0.3 (0.3)
	VBB2N11		0.7 (0.6)
	VBB2N12		1.2 (1.0)
	VBB2N13		2.1 (1.8)
	VBB2N14		3.5 (3.0)
	VBB2N15		4.7 (4.1)
	VBB2N16		7.7 (6.7)
	VBB2N17 <sup>b</sup>		10 (8.7)

b. Full Port Model without characterized disc.

Table-5 3-Way Brass Trim Valve Bodies

Size	Part Number	End Connection	Cv (Kv) A Port	Cv (Kv) B Port
1/2"	VBB3N00	NPT	0.3 (0.3)	0.3 (0.3)
	VBB3N01		0.6 (0.5)	0.8 (0.7)
	VBB3N02		1.0 (.85)	0.8 (0.7)
	VBB3N03		2.0 (1.7)	1.5 (1.3)
	VBB3N04		3.0 (2.6)	1.5 (1.3)
	VBB3N05		4.5 (3.9)	2.7 (2.3)
	VBB3N06		7.3 (6.3)	4.1 (3.5)
	VBB3N07 <sup>b</sup>		10.0 (8.7)	4.8 (4.1)
3/4"	VBB3N10		0.3 (0.3)	0.3 (0.3)
	VBB3N11		0.6 (0.5)	0.8 (0.7)
	VBB3N12		1.0 (.85)	0.8 (0.7)
	VBB3N13		2.0 (1.7)	1.5 (1.3)
	VBB3N14		3.0 (2.6)	1.5 (1.3)
	VBB3N15		4.5 (3.9)	2.7 (2.3)
	VBB3N16		7.3 (6.3)	4.1 (3.5)
	VBB3N17 <sup>b</sup>		10.0 (8.7)	4.8 (4.1)

b. Full Port Model without characterized disc.

## 8. VBB/VBS

Table-6 2-Way Stainless Steel Trim Valve Bodies

Size	Part Number	End Connection	Cv (Kv)
1/2"	VBS2N00	NPT	0.3 (0.3)
	VBS2N01		0.7 (0.6)
	VBS2N02		1.2 (1.0)
	VBS2N03		2.1 (1.8)
	VBS2N04		3.5 (3.0)
	VBS2N05		4.7 (4.1)
	VBS2N06		7.7 (6.7)
	VBS2N07 <sup>b</sup>		10 (8.7)
3/4"	VBS2N10		0.3 (0.3)
	VBS2N11		0.7 (0.6)
	VBS2N12		1.2 (1.0)
	VBS2N13		2.1 (1.8)
	VBS2N14		3.5 (3.0)
	VBS2N15		4.7 (4.1)
	VBS2N16		7.7 (6.7)
	VBS2N17 <sup>b</sup>		10 (8.7)

b. Full Port Model without characterized disc.

Table-7 3-Way Stainless Steel Trim Valve Bodies

Size	Part Number	End Connection	Cv (Kv) A Port	Cv (Kv) B Port
1/2"	VBS3N00	NPT	0.3 (0.3)	0.3 (0.3)
	VBS3N01		0.6 (0.5)	0.8 (0.7)
	VBS3N02		1.0 (.85)	0.8 (0.7)
	VBS3N03		2.0 (1.7)	1.5 (1.3)
	VBS3N04		3.0 (2.6)	1.5 (1.3)
	VBS3N05		4.5 (3.9)	2.7 (2.3)
	VBS3N06		7.3 (6.3)	4.1 (3.5)
	VBS3N07 <sup>b</sup>		10.0 (8.7)	4.8 (4.1)
3/4"	VBS3N10		0.3 (0.3)	0.3 (0.3)
	VBS3N11		0.6 (0.5)	0.8 (0.7)
	VBS3N12		1.0 (.85)	0.8 (0.7)
	VBS3N13		2.0 (1.7)	1.5 (1.3)
	VBS3N14		3.0 (2.6)	1.5 (1.3)
	VBS3N15		4.5 (3.9)	2.7 (2.3)
	VBS3N16		7.3 (6.3)	4.1 (3.5)
	VBS3N17 <sup>b</sup>		10.0 (8.7)	4.8 (4.1)

b. Full Port Model without characterized disc.